

Low Pass Filter

LFCN-EDU2362_5

Surface Mount

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

FV1206


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter	Min.	Typ.	Max.	Units
Passband (Loss < 1.6 dB)	DC	-	2100	MHz
Insertion loss 3dB		2500	-	MHz
Stop Band (30 dB Typ.)	3200	-	6200	MHz
Passband VSWR	-	1.2	-	(:1)
Stopband VSWR	-	17	-	(:1)

Functional Schematic

MAXIMUM RATINGS

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	7.9W



PIN CONNECTIONS

Input	1
Output	3
Ground	2,4