

Coaxial

Low Pass Filter

50Ω DC to 780 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- rugged shielded case
- other NLP models available with wide selection of cut-off frequencies

Applications

- lab use
- test equipment
- video equipment

NLP-850+ NLP-850



CASE STYLE: FF57

Connectors	Model	Price	Qty.
N-Type	NLP-850(+)	\$35.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-780	850	1100-1400 1400-2000	1.7 18


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.67	2.90	.82	grams
17.02	73.66	20.83	90.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$ σ			
10.00	0.02	0.1	10.0	1.00
175.00	0.38	0.1	92.5	1.05
342.50	0.44	0.1	175.0	0.94
507.50	0.18	0.1	257.5	0.95
672.50	0.57	0.1	342.5	0.97
755.00	0.43	0.1	425.0	1.22
780.00	0.40	0.1	507.5	1.35
820.00	1.33	0.6	590.0	1.40
850.00	3.00	0.9	672.5	1.38
1010.00	17.47	1.1	755.0	1.85
1030.00	19.18	1.1	780.0	2.23
1050.00	20.83	1.1	790.0	2.22
1060.00	21.63	1.1	820.0	2.55
1070.00	22.41	1.1	840.0	2.57
1100.00	24.70	1.1	850.0	2.36
1110.00	25.52	1.1	1010.0	0.99
1150.00	28.51	1.2	1020.0	0.92
1350.00	43.25	1.6	1030.0	0.88
1360.00	44.10	1.9	1050.0	0.78
1380.00	45.39	1.8	1060.0	0.75
1400.00	47.43	2.2	1070.0	0.80
1420.00	48.89	2.1	1100.0	0.84
1667.50	69.86	3.1	1110.0	0.70
1750.00	70.13	6.6	1120.0	0.70
1835.00	69.30	4.7	1150.0	0.69
1900.00	67.90	2.7	1300.0	0.45
1920.00	70.63	3.5	1350.0	0.02
1930.00	69.67	2.6	1360.0	0.24
1950.00	74.71	7.2	1380.0	0.48
2000.00	68.74	4.9	1400.0	0.05



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M111708
NLP-850
070626