LFCW-5000+

 50Ω DC to 5 GHz

The Big Deal

- Very good rejection, 40 dB typical
- Rugged, ceramic construction
- Tiny size, 0.063" x 0.032" x 0.024" (0603)
- Good power handling, 2.5W



Generic photo used for illustration purposes only CASE STYLE: JC0603C-1

Product Overview

Mini-Circuits' LFCW-5000+ is an LTCC low pass filter with a passband from DC to 5000 MHz, supporting a variety of applications. This model provides 1.6 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 2.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0603 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Kev Features

| Feature | Advantages |
|--------------------------------------|---|
| Ultra-wide stopband | The LTCC lowpass filter provides a very good stopband rejection until 26.5 GHz suitable for high end applications. |
| LTCC Construction | Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes. |
| Tiny size (0.063" x 0.032" x 0.024") | Saves space in dense circuit board layouts and minimizes the effects of parasitics. |
| Good power handling, 2.5W | Supports a wide range of system power requirements. |
| Wrap-around terminations | Provides excellent solderability and easy visual inspection |

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Low Pass Filter

DC to 5 GHz 50Ω

LFCW-5000+



Generic photo used for illustration purposes only

+RoHS Compliant

Тур.

Max.

Unit

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

CASE STYLE: JC0603C-1

Extremely small size 0603 (0.063" X 0.032" X 0.024") • Temperature stable

• Low loss, 1.6 dB typical Good rejection 40 dB typical


LTCC construction

Applications

Features

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Test and measurements
- Telecommunications and broadband wireless system
- · Military applications
- Satcom modems

Functional Schematic



Parameter

| | Insertion Loss | DC-F1 | DC - 5000 | _ 1.6 2.1 | | dB | |
|-----------|----------------|-------|---------------|------------------|-----|-------|----|
| Pass Band | Freq. Cut-Off | F2* | 5750 | – | 3.0 | 3.0 — | |
| | Return Loss | DC-F1 | DC - 5000 | DC - 5000 — 13 — | | dB | |
| | | F3-F4 | 7200 - 7600 | 20 | 40 | _ | dB |
| Stop Band | Rejection Loss | F4-F5 | 7600 - 11000 | 30 | 43 | _ | dB |
| Stop Band | nejection Loss | F5-F6 | 11000 - 16000 | 25 | 34 | _ | dB |
| | | F6-F7 | 16000 - 26500 | _ | 15 | _ | dB |

Electrical Specifications^{1,2} at 25°C


Frequency (MHz)

^{*} Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

| Maximum Ratings | | | |
|-----------------------|----------------|--|--|
| Operating Temperature | -55°C to 125°C | | |
| Storage Temperature | -55°C to 125°C | | |
| RF Power Input* | 2.5 W @25°C | | |


Passband rating, derate linearly to 0.7W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.


Typical Frequency Response




Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) |
|--------------------|------------------------|---------------------|
| 10 | 0.10 | 43.96 |
| 100 | 0.12 | 35.17 |
| 500 | 0.23 | 26.73 |
| 1000 | 0.31 | 22.76 |
| 1500 | 0.39 | 19.29 |
| 2000 | 0.47 | 17.00 |
| 5000 | 1.41 | 14.36 |
| 5500 | 1.81 | 21.10 |
| 5750 | 2.48 | 13.94 |
| 5890 | 3.03 | 12.93 |
| 6470 | 20.60 | 1.78 |
| 6640 | 30.05 | 1.27 |
| 7000 | 49.58 | 0.85 |
| 7100 | 47.77 | 0.78 |
| 7200 | 47.29 | 0.72 |
| 7600 | 52.56 | 0.57 |
| 8000 | 58.39 | 0.48 |
| 11000 | 55.45 | 0.45 |
| 16000 | 37.03 | 0.28 |
| 26500 | 25.62 | 1.01 |







Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


¹ In Applications where DC voltage and/or current is present at either input or output ports, DC de-coupling capacitors are required. If DC pass from IN-OUT is required, please contact Mini-Circuits for alternatives. 2 Measured on Mini-Circuits Characterization Test Board TB-LFCW-5000+

Pad Connections

| INPUT | 1 |
|--------|------|
| OUTPUT | 3 |
| GROUND | 2, 4 |

Product Marking: F


Demo Board MCL P/N: TB-LFCW-5000+ Suggested PCB Layout (PL-650)



NOTES:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4835 Lo Pro) WITH DIELECTRIC THICKNESS .0107±.0010. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

| Wt. | G | F | Е | D | С | В | Α |
|-------|------|------|------|------|------|------|------|
| grams | .012 | .006 | .028 | .018 | .024 | .032 | .063 |
| .005 | 0.30 | 0.15 | 0.70 | 0.45 | 0.60 | 0.80 | 1.60 |

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

