

## Wideband Amplifier

PMA-183PLN+

 $50\Omega$  6 to 18 GHz

## **THE BIG DEAL**

- · Wideband, 6 to 18 GHz
- Excellent Noise Figure, 1.2 dB at 15 GHz
- Positive Gain Slope
- · High Directivity, 33 dB typ.



Generic photo used for illustration purposes only CASE STYLE: JV2579

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

## **APPLICATIONS**

- C,X & Ku-Band Radar
- Satellite Communication
- ELINT

## **PRODUCT OVERVIEW**

The PMA-183PLN+ is a PHEMT\* based wideband MMIC amplifier with an unique combination of high gain with positive gain slope, high directivity and low noise figure, making it ideal for receiver applications. This design operates on a single 2.6V supply, is well matched for  $50\Omega$  and comes in a tiny, low profile package (3.5 x 2.5 mm, 16-lead MCLP), accommodating dense circuit board layouts.

## **KEY FEATURES**

Feature	Advantages	
High Directivity	With active directivity of 33 dB, the PMA-183PLN+ is an excellent choice for buffering broadband circuits, eliminating the need for an expensive isolator in most cases.	
Positive Gain Slope vs. Frequency • +0.21 dB/GHz (6-15 GHz) • +0.55 dB/GHz (15-18 GHz)	Useful for compesating negative gain slope of most wideband microwave components and eliminating the need for equalization	
Excellent Noise Figure up to 18 GHz • 1.2dB Typ. at 18GHz	Enables lower system noise figure performance.	
3.5 x 2.5mm, 16-lead MCLP package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.	

4.Permanent damage may occur if any of these limits are exceeded.

REV. F ECO-012145 PMA-183PLN+ GY/RS/CP/AM 230106





# Wideband Amplifier PMA-183PLN+

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C, UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	V <sub>S</sub> =2.6V			Units	
Farameter	Condition (WHZ)	Min. Typ.		Max.	Units	
Frequency Range		6		18	GHz	
	6000	20.7	26.3	29.1		
0.1	10000	19.0	26.3	29.6		
Gain	15000	20.8	27.5	30.3	dB	
	18000	-	29.7	-		
	6000		10.2			
	10000		14.8			
nput Return Loss	15000		12.7		dB	
	18000		9.1			
	6000		11.4			
O. Land Balance Land	10000		15.3		15	
Output Return Loss	15000		16.9		dB	
	18000		25.0			
Directivity	6000 - 18000		33		dB	
	6000		9.8			
2.11.	10000		8.6		dBm	
Output Power at 1dB Compression <sup>2</sup>	15000		9.6			
	18000		10.2			
	6000		25			
2.11122	10000		22		ID.	
Output IP3	15000		22.4		dBm	
	18000		21.9			
	6000		1.4			
Notes Plane	10000		1.3		15	
Noise Figure	15000		1.2		dB	
	18000		1.3			
Device Operating Voltage (V <sub>S</sub> )		2.3	2.6	2.9	V	
Device Operating Current (I <sub>DD</sub> )		-	57.2	72	mA	
Device Current Variation vs. Temperature <sup>2</sup>			7.69		μA/°C	
Device Current Variation vs. Voltage³			0.04		mA/mV	
Thermal Resistance, junction-to-ground lead			49.5		°C/W	

<sup>1.</sup> Measured on Mini-Circuits Characterization Test Board TB-PMA-183PLN+. See Characterization Test & Application Circuit (Fig. 1)

## MAXIMUM RATINGS<sup>4</sup>

Parameter	Ratings	
Operating Temperature (ground lead)	-40°C to 85°C	
Storage Temperature	-65°C to 150°C	
Junction Temperature	131°C	
Total Power Dissipation	0.9W	
Input Power (CW), Vs=2.6V	+24 dBm (5 minutes max.) +13 dBm (continuous)	
DC Voltage on Vs	4V	
DC Voltage on RF Ports (RF-IN & RF-OUT)	4V	

<sup>4.</sup>Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.




<sup>2.</sup> Device Current Variation vs. Temperature= (Current in mA at 45°C- Current in mA at 45°C/130°C

3. Device Current Variation vs. Voltage = (Current in mA at 2.9V – Current in mA at 2.3V) / ((2.9V-2.3V)\*1000 mA/mV)

# Wideband Amplifier PMA-183PLN+

## SIMPLIFIED SCHEMATIC & PAD DESCRIPTION



Function	Pad Number	Description (See Figure 1)
VDD	2	Supply Voltage Pad, Connects to Vs via R1
VE	4	Enable Voltage Pad, Connects to VDD via R2
RF-IN	7	RF Input Pad, Connects to the input port
RF-OUT	15	RF Output Pad, Connects to the output port
NC	1,3,5 & 9-13	No connection to the die, Grounded on the test board
GROUND	6,8,14,16 & Paddle	Connects to ground on Test board

## **CHARACTERIZATION TEST & APPLICATION CIRCUIT**





Fig 1. Application and Characterization Circuit

Note: This block diagram is used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-PMA-183PLN+) Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

- 1. Gain and Return loss: Pin= -25dBm
- 2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -10 dBm/tone at output.

Component	Size	Value	Part Number	Manufacturer
C1, C4	0805	0.33uF	TAJR334K035RNJ	AVX
C2, C5	0603	1000pF	GCM1885C1H102JA16D	Murata
C3, C6	0402	100pF	GRM1555C1H101JA01D	Murata
R1	0603	10 Ohm	ESR03EZPF10R0	Rohm Semiconductor
R2	0402	180 Ohm	RK73H1ETTP1800F	KOA Speer

## **PRODUCT MARKING**



Marking may contain other features or characters for internal lot control



## Wideband Amplifier PMA-183PLN+

## ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS


**CLICK HERE** 

	Data Table
Performance Data	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	JV2579 Plastic package, exposed paddle, lead finish: Matte-Tin Plate
Tape & Reel	F104
Standard quantities available on reel	7" reels with 2K devices
Suggested Layout for PCB Design	PL-691
Evaluation Board	TB-PMA-183PLN+ & TB-PMA-183PLNC+
Environmental Ratings	ENV08T1

### **ESD RATING**

Human Body Model (HBM): Class 1C (1000 to <2000V) in accordance with ANSI/ESD STM 5.1 - 2001

### **MSL TEST FLOW CHART**



- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp