# Surface Mount **Low Pass Filter**

50Ω DC to 50 MHz

## The Big Deal

- Good passband Insertion loss, 0.8 dB typical
- High rejection, 50 dB from 70-2000 MHz
- Fast roll-off
- Miniature shielded package



#### CASE STYLE: H71198

## **Product Overview**

The LPF-B50+ is a lowpass filter in a shielded package (size of 0.472" x 0.826" x .22") fabricated using SMT technology. Covering DC-50 MHz band width, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

## **Key Features**

Feature	Advantages
Low frequency and good passband Insertion loss, 0.8 dB typical	Low insertion loss will be used in designs optimized for high performance applications.
Fast roll-off	Fast roll-off, this will attenuate frequencies closer to the passband with good rejection value of 72 dB.
Good ultimate rejection	This enables the filters to attenuate spurious signals and reject harmonics for broadband frequency.

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



# Surface Mount **Low Pass Filter**

#### **50**Ω DC to 50 MHz

# LPF-B50+



CASE STYLE: HZ1198

Тур.

0.8

3.5

1.2

36

18

Max.

2

1.5

Unit

dB

dB

:1

dB

:1

Group Delay

Min.

\_

20

#### **Features**

- High rejection, 36 dB typical
- · Sharp insertion loss roll-off
- Shielded case
- Aqueous washable

### **Applications**

- Defence communications
- Transmitters / receivers
- · Harmonic rejection

Maximum	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to +100°C
RF Power Input	1 W max.

Parameter

Pass Band

Stop Band

Insertion Loss

Rejection Loss


Freq. Cut-Off

VSWR


VSWR

Permanent damage may occur if any of these limits are exceeded

### **Functional Schematic**



### **Typical Frequency Response**



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site

for RoHS Compliance methodologies and qualifications

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Dela (nsec)
1.0	0.09	1.03	1.00	15.67
14.0	0.18	1.09	5.00	15.67
30.0	0.28	1.10	10.00	15.83
40.0	0.41	1.07	13.00	16.09
50.0	0.73	1.10	15.00	16.28
54.0	1.40	1.50	18.00	16.74
55.0	2.21	2.14	20.00	17.09
56.0	3.95	3.57	23.00	17.61
57.0	6.86	6.30	25.00	18.06
59.0	14.69	14.03	28.00	18.83
62.0	27.08	21.20	30.00	19.53
65.0	39.46	24.83	33.00	20.75
71.0	67.01	30.49	35.00	21.75
75.0	70.91	33.42	38.00	23.51
100.0	68.31	54.29	40.00	24.95
500.0	73.95	217.15	43.00	27.73
1500.0	66.89	69.49	45.00	30.21
2000.0	68.96	49.64	47.00	33.54
3000.0	60.90	41.37	48.00	35.73
3300.0	45.95	31.60	50.00	41.43

Electrical Specifications at 25°C

Frequency (MHz)

DC-50

55

DC-50

65-3300

65-3300

Typical Performance Data at 25°C

F#


DC-F1


F2


DC-F1

F3-F4

F3-F4







#### Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A M160153 BPF-B50+ EDR-10131AU URJ/NY 161230 Page 2 of 3


## Low Pass Filter



#### **Pad Connections**

INPUT	1
OUTPUT	2
GROUND	3,4,5,6

Demo Board MCL P/N: TB-400+ Suggested PCB Layout (PL-247)




#### NOTES:


- 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC

1. A.

- (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

#### **Outline Drawing**





METALLIZATION [:::::] SOLDER RESIST Suggested Layout, Tolerance to be within ±.002

#### Outline Dimensions ( inch )

А	В	С	D	E	F	G	н	J	ĸ	L	M
.472	.826	.220	.551	.118	.047	.078	.076	.142	.543	.078	.236
11.99	20.98	5.59	14.00	3.00	1.19	1.98	1.93	3.61	13.79	1.98	5.99
N	P	Q	S	т	U	V	W	х	Y		wt
N .079	P .138	Q .162	S .098	T .096	U .217	V .067	W .157		Y .512		wt grams
		_	.098		-		.157				

Notes

- Notes
  A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the refits and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

