

Engineering Development Model


Voltage Controlled Oscillator

POS-ED4638/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : A06

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	322		473	MHz
Tuning Voltage	0.5		7	V
Power Output		+4		dBm
Phase Noise				
at 1 kHz offset		-77		dBc/Hz
at 10 KHz offset		-98		dBc/Hz
at 100 KHz offset		-121		dBc/Hz
at 1000 kHz offset		-139		dBc/Hz
Pulling at 12 dBm PK-PK all phases		1.4		MHz
Pushing at Vcc=5V±0.25V		1.3		MHz/V
Tuning Sensitivity		20 - 30		MHz/V
Harmonic Suppression		-23		dBc
3 dB Modulation Bandwidth		50		kHz
Supply Voltage		5		V
Supply Current			20	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7V
Absolute Tuning Voltage (Vtune)	+9V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	8
GROUND	3,4,5,6,7