

Non-Catalog Model

Frequency Mixer

LRMS-2R

Level 7 (LO Power +7 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : QQQ130

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	5		1000	MHz
	RF (fL to fU)	5		1000	MHz
	IF	0		1000	MHz
Conversion Loss	mid band		6.6	8.0	dB
	Total Range			10.0	dB
LO-RF Isolation	Low Range	40	55		dB
	Mid Range	20	39		dB
	Upper Range	17	22		dB
LO-IF Isolation	Low Range	35	46		dB
	Mid Range	20	30		dB
	Upper Range	11	18		dB
1 dB Comp. Input Power			+1		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

Phase detection, positive polarity

Hermetic sealed diodes

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	1
RF	4
IF	5
GROUND	2, 3, 6

Electrical Schematics

