

Surface Mount

Power Splitter/Combiner

2 Way-0° 50Ω 20 to 2000 MHz

LRPS-2-11A+


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

SUM PORT	6
PORT 1	4
PORT 2	3
GROUND	1,2,5

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch)

A	B	C	D	E	F	G
.380	.32	.215	.100	.040	.060	.195
9.65	8.13	5.46	2.54	1.02	1.52	4.95

H	J	K	L	M	N	wt
0.25	.110	.070	.420	.120	.060	grams
6.35	2.79	1.78	10.67	3.05	1.52	0.43

Demo Board MCL P/N: TB-480+ Suggested PCB Layout (PL-290)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
4. DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- very wideband, 20 to 2000 MHz
- low insertion loss, 0.7 dB typ.
- good isolation, 21 dB typ.

Applications

- cellular
- GPS
- communications systems



Generic photo used for illustration purposes only

CASE STYLE: QQQ1358

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 3.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L	M	U	L	M	U	L	M	U	L	M	U	L	M	U	L	M	U
f _L -f _U	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
20-2000	19	15	21	15	30	15	0.6	0.8	0.7	1.0	0.8	1.5	2.0	3.0	5.0	0.2	0.3	0.7

L = 20-200 MHz M = 200-1000 MHz U = 1000-2000 MHz

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
20.00	3.54	3.54	0.00	19.18	0.01	1.99	1.58	1.58
140.00	3.58	3.58	0.01	19.39	0.23	1.96	1.59	1.59
200.00	3.59	3.59	0.01	19.49	0.35	1.95	1.59	1.59
400.00	3.62	3.60	0.02	19.96	0.62	1.92	1.58	1.58
800.00	3.63	3.56	0.07	21.25	1.00	1.81	1.54	1.53
900.00	3.63	3.54	0.09	21.81	1.29	1.76	1.52	1.51
1000.00	3.60	3.51	0.09	22.43	1.52	1.72	1.50	1.50
1100.00	3.60	3.49	0.10	23.16	1.30	1.67	1.49	1.48
1200.00	3.61	3.48	0.12	23.85	1.28	1.62	1.47	1.46
1400.00	3.63	3.46	0.17	24.72	1.01	1.51	1.43	1.43
1500.00	3.64	3.45	0.19	24.59	1.10	1.46	1.41	1.41
1700.00	3.68	3.44	0.24	22.76	0.92	1.38	1.36	1.39
1800.00	3.71	3.46	0.25	21.43	0.76	1.36	1.34	1.38
1900.00	3.76	3.49	0.27	20.06	0.54	1.37	1.32	1.37
2000.00	3.84	3.53	0.30	18.74	0.23	1.41	1.31	1.37

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
LRPS-2-11A+
ED-13379/3
HY/AM
201117
Page 1 of 1