Low Noise, High IP3

Monolithic Amplifier

PSA-545+

0.05 to 4 GHz 50Ω

CASE STYLE: CA1389

The Big Deal

- Ultra Low Noise Figure, 0.8 dB
- High IP3
- Wideband, up to 4 GHz
- Low Additive Phase Noise
- Suitable for Low Phase Noise Applications

Product Overview

Mini-Circuits PSA-545+ is a E-PHEMT based Ultra-Low Noise MMIC Amplifier operating from 50 MHz to 4 GHz with a unique combination of low noise and high IP3 making this amplifier ideal for sensitive receiver applications. This design operates on a single 3V supply at only 80mA and is internally matched to 50 ohms.

Key Features

Feature	Advantages		
Ultra Low Noise, 0.8 dB	Outstanding Noise Figure, measured in a 50 Ohm environment without any external matching		
High IP3, 36 dBm	Combining Low Noise and High IP3 makes this MMIC amplifier ideal for Low Noise Receiver Front End (RFE) because it gives the user advantages at both ends of the dynamic range: sensitivity & two-tone spur-free dynamic range		
High Output Power, +20 dBm	The PSA-545+ provides up to +20dBm output power at 1dB compression enabling this amplifier to support high linear dynamic range requirements		
Broad Band	Operating over a broadband the PSA-545+ covers the primary wireless communications bands: Cellular, PCS, LTE, WiMAX		
Internally Matched	No external matching elements required to achieve the advertised noise and output powe over the full band		
SOT-363 Package	Small size, industry standard package		
Max Input Power, +15dBm	Ruggedized design operates up to input powers of +15dBm without the need of an externil limiter		
High Reliability	Low, small signal operating current of 80mA nominal maintains junction temperatures typically below 125°C at 85°C ground lead temperature		
Low Additive Phase Noise, Typically -164.5dBc/Hz at 10kHz Offset	Ideal for low phase noise synthesizer applications		

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Monolithic Amplifier

PSA-545+

0.05 to 4 GHz 50Ω

Product Features

- Single Positive Supply Voltage, +3V, Id=80mA
- Ultra Low Noise Figure, 0.8 dB typ. at 1 GHz
- High IP3, up to 35 dBm typ. at 1 GHz
- Output Power at 1dB comp., up to +20 dBm typ.
- Gain, 20 dB typ. at 1GHz
- Micro-miniature size SOT-363 package
- Aqueous washable
- Low additive phase noise

Typical Applications

- Cellular
- ISM
- GSM
- WCDMA
- LTE
- WiMax
- WLAN
- UNII and HIPERLAN

CASE STYLE: CA1389


+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

General Description

PSA-545+ is an advanced wide band, high dynamic range, low noise, high IP3, high output power, monolithic amplifier. Manufactured using E-PHEMT* technology enables it to work with a single positive supply voltage.

simplified schematic and pin description





Function	Pin Number	Description (See Application Circuit, Fig. 2)	
RF IN	3	RF input pin (connect to pin 4 via L2)	
RF-OUT & Vd	6	RF output pin (connected to RF-out via blocking cap C2 and supply voltage Vd via RF Choke L1)	
BIAS	4	Connected to Vs via Rbias. (Connect to ground via C4 & R1)	
GND	1,2,5	Connections to ground	

^{*} Enhancement mode pseudomorphic High Electron Mobility Transistor.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Electrical Specifications⁽¹⁾ at 25°C, Zo=50Ω, (refer to characterization circuit, Fig. 1)

Parameter	Condition (GHz)	Min.	Тур.	Max.	Units
Frequency Range		0.05		4.0	GHz
at DC Volts (Vd)			3.0		V
DC Current (Id) ⁽⁶⁾		60	80	100	mA
Bias Current (I _{Rbias})			5.6		mA
Noise Figure	0.05 0.5 1.0 2.0 3.0 4.0		2.1 0.7 0.8 1.0 1.3 1.7	 1.3 	dB
Additive Phase Noise 2.0GHz, 10kHz		_	-164.5		kHz
Gain	0.05 0.5 1.0 2.0 3.0 4.0	17.8 — — — —	24.8 23.5 19.8 14.9 12.1 10.4	21.8 — — — —	dB
Input Return Loss	0.05-0.5 0.5-4.0		8		dB
Output Return Loss	0.05-0.2 0.2-4.0		12 18		dB
Output IP3	0.05 0.5 1.0 2.0 3.0 4.0		34.4 34.9 35.4 36.2 36.3 35.4		dBm
Output Power @1dB compression ⁽²⁾	0.05 0.5 1.0 2.0 3.0 4.0		19.6 19.6 19.5 20.2 20.5 20.5		dBm
DC Current Variation Vs. Temperature ⁽³⁾			-0.064		mA/°C
Thermal Resistance ⁽⁵⁾			165		°C/W

Absolute Maximum Ratinge(4)

Absolute Maximum hattings.				
Parameter	Ratings			
Operating Temperature ⁽⁵⁾	-40°C to 85°C			
Storage Temperature	-65°C to 150°C			
Channel Temperature	150°C			
DC Voltage (Pin 6)	5V			
Device Current (Pin 6)	130 mA			
Power Dissipation	390 mW			
Bias Reference Current (Pin 4)	10 mA			
Input Power (CW) (Pin 3) (7)	15 dBm			

⁽¹⁾ Measured on Mini-Circuits Characterization test board TB-533+.

See Characterization Test Circuit (Fig. 1) (2) Current increases at P1dB

^{(3) (}Current at 85°C - Current at -45°C)/130

⁽⁴⁾ Permanent damage may occur if any of these limits are exceeded.

These maximum ratings are not intended for continuous normal operation.

(5) Defined with reference to ground pad temperature.

⁽⁶⁾ Specified DC current consumption is under small signal conditions. Current will increase with input RF Power. To maintain maximum current consumption, external DC current limiting circuits are required on Vd line.

⁽⁷⁾ Maximum input power is specified based upon external Vd current limiting of 100 mA. Maximum input power will degrade without external current limiting.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization Test Board TB-533+) Gain, Return loss, Output power at 1dB compression (P1 dB), Output IP3 (OIP3) and Noise Figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

- 1. Gain: Pin= -25dBm
- 2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

Recommended Application Circuit

(refer to evaluation board for PCB Layout and component values)





Fig 2. Recommended Application Circuit Note: Resistance of L1, 0.1-0.2Ω typically

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Product Marking



Marking may contain other features or characters for internal lot control

Additional Detailed Technical Information

Additional information is available on our web site www.minicircuits.com. To access this information enter the model number on our web site home page.

Performance data, graphs, s-parameter data set (.zip file)

Case Style: CA1389

Plastic molded SOT-363 package, lead finish: matte tin

Tape & Reel: F101

Standard quantities availabe on reel: 7" reels with 20, 50, 100, 200, 500, 1K, or 2K devices.

Suggested Layout for PCB Design: PL-311

Evaluation Board: TB-534+

Environmental Ratings: ENV08T2

ESD Rating


Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (<100V) in accordance with ANSI/ESD STM5.2-1999; passes 40V

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL Test Flow Chart



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp