## ULTRA·REL® Ceramic Hermetic

# **Frequency Mixers**

# **MAC Series**

300 MHz to 12 GHz LO Levels 4 to 17 dBm

### **The Big Deal**

- 3-Year Guarantee
- Hermetically sealed LTCC construction
- Low-profile case, 0.06" high
- Priced for outstanding VALUE



CASE STYLE: DZ1650

### **Product Overview**

Mini-Circuits MAC mixers employ a unique new design and a highly repeatable, tightly controlled, automated process that delivers industry-leading reliability at a remarkably affordable price. Schottky diode quads meeting our strict specifications are bonded to a multilayer integrated LTCC substrate, and then hermetically sealed under a controlled atmosphere with gold-plated covers and eutectic AuSn solder. These passive, double-balanced mixers have been tested to MIL requirements for gross leak, fine leak, thermal shock, vibration, acceleration, mechanical shock, and HTOL, and every MAC mixer is backed with our 3-year guarantee.

#### Click here for more about the MAC mixer

### **Key Features**

Feature	Advantages
Low, Flat Conversion Loss	No need to compensate for variations over frequency.
Hermetically Sealed	Ideal for use anywhere long-term reliability adds bottom-line value: high moisture areas, busy production lines, high-speed distribution centers, heavy industry, outdoor settings, and unmanned facilities, as well as military applications.
Rugged LTCC/Hermetic Construction	Demonstrated reliability in harsh, physically abusive environments with high vibration, acceleration, and/or mechanical shock.
Wide Operating Temperature Range	Guaranteed performance from -55 to +125°C. MAC mixers have also passed thermal shock testing from -55 to +150°C, through 1000 cycles, 15 minutes per cycle.
Exposed Termination Ends	Our unique case design allows for easy visual inspection of side solder fillets per IPC-A-610 section 8.3.4.6, and features gold-plated terminations for excellent solderability.
Incredible Performance/Price	Game-changing affordability brings Hi-Rel hermetic mixers within the reach of commercial budgets.

#### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

# Frequency Mixer wide BAND

## MAC-80LH+

Generic photo used for illustration purposes only

CASE STYLE: DZ1650

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site

### Level 10 (LO Power+10 dBm) 2800 to 8000 MHz

#### **Maximum Ratings**

Operating Temperature	-55°C to 125°C		
Storage Temperature	-65°C to 150°C		
RF Power	50 mW		
IF Current	40 mA		
Permanent damage may occur if any of these limits are exceeded.			

## Pin Connections

LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9

#### **Features**

- wide bandwidth, 2800 to 8000 MHz
- low conversion loss, 5.5 dB typ.
- high L-R isolation, 29 dB typ.
- LTCC double balanced mixer
- · aqueous washable
- low cost
- low profile, 0.060"
- protected by US Patent 7,027,795
- 3-YEAR GUARANTEE -The Most Reliable Mixers


### Applications


- satellite up and down converters
- line of sight links
- · defense radar
- defense communications

# for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500,1000

### **Outline Drawing**





Parameter	Condition (MHz)	Min.	Тур.	Max.	Units
Frequency Range, LO/RF			2800 - 8000		MHz
Frequency Range, IF			DC - 1250		MHz
Conversion Loss*	2800 - 5000	_	5.5	7.6	dB
Conversion Loss	5000 - 8000	_	5.6	7.3	uБ
LO to BE Isolation	2800 - 5000	28	39	_	dB
LO to HE ISOIATION	5000 - 8000	25	39	_	uБ
LO to IF Isolation	2800 - 5000	8	14	_	dB
LO to IF Isolation	5000 - 8000	5000 - 8000 15 27		_	ub
IP3	2800 - 5000	_	16	_	dBm
IP3	5000 - 8000	_	12	_	UDIII
RF Input Power at 1 dB Compression	2800 - 8000		+5		dBm

Electrical Specifications at 25°C

\*Conversion Loss measured at 30 MHz IF


#### Outline Dimensions (inch )

A .30	B .250	C .060	D	.050	F .050	G .030
7.62	6.35	1.52		1.27	1.27	0.76
Н	J	K	L	М		wt
.056		.085	.270	.035		grams
1.42		2.16	6.86	0.89		0.29

### Typical Performance Data at 25°C and LO=+10dBm

	Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
			LO	LO	LO	LO	LO
	RF	LO	+10dBm	+10dBm	+10dBm	+10dBm	+10dBm
	00004	0000.4	0.00	40.00	0.07	0.70	0.54
	2800.1	2830.1	6.39	43.36	9.87	2.73	2.51
	3100.1	3130.1	5.69	44.18	11.81	2.45	2.68
	3400.1	3430.1	5.43	41.44	13.40	1.80	2.66
	3700.1	3730.1	5.01	35.92	14.03	1.64	2.55
	4000.1	4030.1	6.80	45.38	13.34	3.29	2.48
	4400.1	4430.1	6.42	29.90	16.92	1.99	2.49
	4600.1	4630.1	7.15	31.54	20.49	2.67	2.53
	5000.1	5030.1	6.17	35.24	24.01	2.21	2.26
	5200.1	5230.1	5.84	36.23	24.96	1.97	2.32
	5400.1	5430.1	5.44	38.33	25.44	1.82	2.33
	5800.1	5830.1	6.49	44.80	27.72	2.91	2.17
	6000.1	6030.1	6.06	53.01	29.00	2.84	2.35
	6400.1	6430.1	5.80	41.29	32.09	2.31	2.43
	6600.1	6630.1	5.73	38.42	32.95	2.23	2.55
	7000.1	7030.1	5.51	33.64	26.64	1.81	1.84
	7200.1	7230.1	5.38	32.03	22.36	1.51	1.78
	7400.1	7430.1	5.32	31.37	18.67	1.48	1.78
	7600.1	7630.1	5.57	31.16	16.75	1.39	1.90
	7800.1	7830.1	5.82	28.30	15.31	1.46	2.14
	8000.1	8030.1	5.78	27.20	16.47	1.55	2.51
	1	2200	3.70	0			=.0.


#### Demo Board MCL P/N: TB-956+ Suggested PCB Layout (PL-045)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .0.20" ± .0015"; COPPER: 1/2 .02. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE POB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


#### **Electrical Schematic**





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp





















A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

### Designed and Built for Long-Term Reliability in **HOSTILE ENVIRONMENTS**



#### Qualification Testing

The table below shows the initial qualification testing performed. If required, parts can be subjected to 100% screening and qualifications testing per MIL standard requirement.

Gross Leak	MIL-STD-202 Method 112, Condition D
	(100% of all MAC Mixers we ship)

Fine Leak	MIL-STD-202 Method 112, Condition C,
	Procedure IIIa

Thermal Shock MIL-STD-202 Method 107

> (-55/+100C°, 1000 cycles, 15 minutes) (-55/+150C°, 1000 cycles, 15 minutes)

**Vibration** MIL-STD-202 Method 204, Condition D

(10-2000Hz sine, 20g, 3 axis, 12 c.y.ea.)

Acceleration MIL-STD-883 Method 2001, Condition E

Mechanical Shock MIL-STD-202 Method 213, Condition A

**HTOL** MIL-STD-202 Method 108, Condition D (1000 hours, 125°C, at rated LO level)

Multiple Reflow JESD22-B102

**Bend Test** JESD22-B113

Adhesion Strength Push test >10lb









All Photos courtesy of U.S. Military and NASA

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp