

Frequency Mixer

MACA-ED10457/8

Level -3 (LO Power -3 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.


CASE STYLE : DZ1034

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	500		2480	MHz
	RF (f _L to f _U)	500		2480	MHz
	IF	10		500	MHz
Conversion Loss	Total Range		6.95		dB
LO-RF Isolation			20		dB
LO-IF Isolation			51		dB
Input IP3			+20		dBm
1 dB Compression			+10		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	10
RF	5
IF	3
DC	7
GROUND EXT	1,2,4,6,8,9

Electrical Schematics



LFCN-490+ is added to improve L-I isolation.