# Surface Mount **Monolithic Amplifier**

## DC-2 GHz

### **Product Features**

- Wideband, DC to 2 GHz
- Exact footprint substitute for Avago's MSA-0286
- Internally Matched to 50 Ohms
- Unconditionally stable
- Protected by US Patent, 6,943,629

## **Typical Applications**

- Cellular
- PCN instrumentation
- VHF/UHF receivers/transmitters




## MAR-2SM+ CASE STYLE: WW107


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## **General Description**

MAR-2SM+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in a Micro-X package. MAR-2SM+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 10,000 years at 85°C case temperature.

#### simplified schematic and pin description





Function	Pin Number	Description
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are entitled to be excluded and benefits contained in the specification are entitled to be excluded and benefits contained in the specification document are not the specification and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV D M151107 MAR-2SM+ 200930 Page 1 of 4



#### Electrical Specifications at 25°C and 25mA, unless noted

Parameter		Min.	Тур.	Max.	Units
Frequency Range*		DC		2	GHz
Gain	f=0.1 GHz	_	12.5	_	dB
	f=1 GHz	—	12.0	_	
	f=2 GHz	8.5 <sup>2</sup>	11.0	_	
Input Return Loss	f=DC to 2 GHz		17.5		dB
Output Return Loss	f=DC to 2 GHz		17.5		dB
Output Power @ 1 dB compression	f=1 GHz		+7		dBm
Output IP3	f=1 GHz		+22		dBm
Noise Figure	f=1 GHz		3.7		dB
Recommended Device Operating Current			25		mA
Device Operating Voltage			5.0		V
Device Voltage Variation vs. Temperature at 25 mA			-2.7		mV/°C
Device Voltage Variation vs. Current at 25°C		16.7		mV/mA	
Thermal Resistance, junction-to-case <sup>1</sup>		164		°C/W	

\*Guaranteed specification DC-2 GHz. Low frequency cut off determined by external coupling capacitors.

#### **Absolute Maximum Ratings**

Parameter	Ratings	
Operating Temperature	-40°C to 85°C	
Storage Temperature	-55°C to 100°C	
Operating Current	60mA	
Power Dissipation	325mW	
Input Power	13dBm	

Note: Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation. <sup>1</sup>Case is defined as ground leads. <sup>2</sup>Full temperature range.


Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits: website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



## **Product Marking**



Markings in addition to model number designation may appear for internal quality control purposes.

#### Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

#### Performance data, graphs, s-parameter data set (.zip file)

#### Case Style: WW107

Plastic micro-x, .085 body diameter, lead finish: tin/silver/nickel

#### Tape & Reel: F4


7" Reels with 20, 50, 100, 200, 500, 1K devices 13" Reels with 2K, 4K devices

#### Suggested Layout for PCB Design: PL-253

Evaluation Board: TB-411-2+

#### **Environmental Ratings: ENV08T3**

## **Recommended Application Circuit**



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS					
Vcc	"1%" Res. Values (ohms for Optimum Biasing				
7	80.6				
8	121				
9	162				
10	200				
11	243				
12	280				
13	324				
14	357				
15	402				

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Min-Circuit's tapplicable established test performance data and measurement instructions.
to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Min-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp





## ESD Rating

Human Body Model (HBM): Class 1B (500 v to < 1000 v) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M1 ( <100 v) in accordance with ANSI/ESD STM 5.2 - 1999

### **MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

## **MSL Test Flow Chart**



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and beefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com