

Non-Catalog Model

Power Splitter/Combiner

QBA-22

2 Way-90°

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : SM1

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		1800		2400	MHz
Isolation	1800 - 2400 MHz	13	18		dB
Insertion Loss					
Average of Coupled Outputs	1800 - 2400 MHz		0.60	1.00	dB
above 3.0 dB					
Phase Unbalance	1800 - 2400 MHz		1.065	5.000	deg.
Amplitude Unbalance	1800 - 2400 MHz		0.446	1.000	dB
VSWR	SUM Port		1.27		(:1)
	OUT Ports		1.33		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	10(0)
PORT 2	6(-90)
GND EXT	2, 3, 4, 7, 8, 9
ISOLATE	5

Functional Diagram

