

Engineering Development Model

Power Splitter/Combiner

2 Way-90°

QCN-ED11876B/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.




CASE STYLE : FV1206-1

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		400		760 MHz
Isolation	400-760 MHz		16	dB
Insertion Loss Average of Coupled Outputs above 3.0 dB	400-760 MHz		0.55	dB
Phase Unbalance	400-760 MHz		2.25	deg.
Amplitude Unbalance	400-760 MHz		0.25	dB
VSWR	SUM Port		1.36	(:1)
	OUT Ports		1.38	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1 (0°)	4
PORT 2 (90°)	6
50 TERM. EXTERNAL	3
GND	2,5

Functional Diagram



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



REV. X2
QCN-ED11876B/2
8/12/2010
Page 1 of 1