

Power Splitter/Combiner

QCS-ED13415/3

2 Way-90°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : GE0805C-1

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		3100		5900 MHz
Isolation	3100-5900 MHz		24	dB
Insertion Loss Average of Coupled Outputs above 3.0 dB	3100-5900 MHz		0.50	dB
Phase Unbalance	3100-5900 MHz		2.40	deg.
Amplitude Unbalance	3100-5900 MHz		0.35	dB
VSWR	SUM Port		1.20	(:1)
	OUT Ports		1.20	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1 (0°)	4
PORT 2 (90°)	6
50 TERM. EXTERNAL	3
GND	2,5

Functional Diagram

