

Frequency Mixer

MCA-ED12846/1

Level 17 (LO Power + 17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DZ883

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	710.1		3710.1	MHz
	RF (f _L to f _U)	710.1		3710.1	MHz
	IF	10		650	MHz
Conversion Loss	Total Range		7.86		dB
LO-RF Isolation			36		dB
LO-IF Isolation			30		dB
Input IP3			+26		dBm
1 dB Compression			+17		dBm

MAXIMUM RATINGS	
Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9

Electrical Schematics

