

Surface Mount Attenuator/Switch

RAS-2-75+

75Ω Bi-Phase 10 to 1000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Control Current	30mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	4
OUTPUT	1
CONTROL	5
GROUND	2,3,6

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.250	.31	.275	.100	.050	.055
6.35	7.87	6.99	2.54	1.27	1.40
G	H	J	K	wt	
.040	.070	.270	.050	grams	
1.02	1.78	6.86	1.27	0.50	

Features

- wideband, 10 to 1000 MHz
- excellent phase and amplitude unbalance

Applications

- bi-phase modulator



Generic photo used for illustration purposes only

CASE STYLE: TT241

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Attenuator/Switch Electrical Specifications


FREQUENCY (MHz)	INSERTION LOSS (dB) ±20 mA	MAX. INPUT PWR (dBm) ±20 mA	IN-OUT ISOLATION (dB) 0 mA						BI-PHASE X (±20 mA) Typ.						
			L		M		U		ΔAMP (dB)		Phase (deg.) deviation from 180°				
IN	CON	Mid-Band m	Total Range	1 dB compr.	no damage	Typ.	Min.	Typ.	Min.	Typ.	Min.	Total Range	Total Range		
10-1000	DC-0.05	4.1 6.0	4.5 7.5	20	25	58	40	42	28	39	20	0.15	0.3	1.5	3.0

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U] m = [$2 f_L$ to $f_U/2$]
Performance specifications apply for input power up to 10 dB below stated 1 dB compression.

suggested control port biasing configuration





electrical schematic



Typical Performance Data

Freq. (MHz)	I. Loss (dB) at 20mA		±Control ΔAMP (dB)		20mA ΔPhase (in-out) (deg.)		Isolation (dB) (in-con)		Input R. Loss (dB)	Control Current (mA)	Attenuation (dB)			Phase Δ ref at 15mA Ctrl (deg.)			Input VSWR		
	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ			10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz
10.0	3.85	0.03	0.02	0.02	179.9	68	41	10.1	0.0000	72.9	42.4	27.4	77.0	123.7	-103.5	2.1	3.1	3.1	
11.1	3.82	0.03	0.02	0.02	179.9	68	40	10.2	0.0003	55.2	42.7	27.4	11.3	120.0	-102.9	2.1	3.1	3.1	
18.9	3.74	0.03	0.02	0.02	179.9	63	36	10.6	0.0005	53.2	42.9	27.5	7.8	118.9	-102.6	2.1	3.1	3.1	
20.0	3.74	0.03	0.02	0.02	180.0	63	35	10.7	0.0012	51.4	43.0	27.5	3.9	117.5	-102.4	2.1	3.1	3.1	
31.6	3.76	0.02	0.02	0.02	180.0	60	31	10.7	0.0020	48.6	43.5	27.5	-0.2	112.3	-101.5	2.1	3.1	3.1	
88.8	3.89	0.03	0.02	0.02	179.9	51	23	10.3	0.0057	43.1	45.3	27.5	1.3	90.0	-98.1	2.1	3.1	3.0	
100.0	3.92	0.03	0.02	0.02	179.9	50	22	10.2	0.0100	39.5	44.9	27.5	3.7	57.7	-94.3	2.0	3.1	3.0	
249.1	4.03	0.04	0.03	0.03	179.8	42	16	8.9	0.0159	36.4	42.4	27.5	5.1	30.2	-89.7	2.0	3.1	3.0	
297.8	4.07	0.05	0.03	0.03	179.8	41	15	8.5	0.0285	31.8	36.4	27.2	6.5	7.1	-79.2	2.0	3.0	2.9	
417.3	4.11	0.07	0.05	0.05	179.6	38	15	7.9	0.0446	28.2	32.0	26.8	7.2	-1.1	-68.6	1.9	2.9	2.8	
498.9	4.00	0.08	0.06	0.06	179.2	37	16	7.9	0.0715	24.6	27.7	25.4	7.4	-5.8	-54.2	1.8	2.8	2.7	
596.4	3.94	0.09	0.08	0.08	178.5	37	18	8.5	0.1020	21.8	24.5	23.6	7.5	-7.7	-43.6	1.7	2.7	2.6	
699.0	3.81	0.10	0.11	0.11	177.8	36	20	10.0	0.1879	17.4	19.7	20.0	7.0	-9.0	-27.2	1.5	2.5	2.4	
756.8	3.86	0.12	0.11	0.11	177.5	36	19	11.1	0.3050	14.2	16.2	16.9	6.3	-8.9	-17.7	1.4	2.3	2.2	
787.4	3.89	0.14	0.15	0.15	177.4	35	18	12.0	0.4255	12.2	14.0	14.9	5.7	-8.5	-12.5	1.2	2.1	2.0	
887.0	4.40	0.24	0.24	0.24	176.4	35	13	13.7	0.7057	9.7	11.2	12.3	4.5	-7.4	-6.6	1.1	2.0	1.8	
941.4	4.82	0.31	0.39	0.39	175.6	35	11	15.6	0.9950	8.3	9.6	10.9	3.7	-6.6	-3.4	1.2	1.9	1.6	
979.5	5.15	0.36	0.39	0.39	175.1	35	9	15.2	1.7446	6.5	7.4	9.2	2.5	-4.9	0.2	1.4	1.8	1.5	
999.1	5.30	0.38	0.40	0.40	175.0	35	9	14.5	5.6985	4.4	4.8	7.6	0.6	-1.6	1.8	1.8	1.8	1.2	
1019.2	5.47	0.41	0.45	0.45	175.1	35	8	13.8	15.0090	3.7	3.9	7.3	0.0	0.0	0.1	2.1	1.9	1.1	



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

