

# Voltage Controlled Oscillator **MOS-1797-119+**

50Ω    1618 to 1797 MHz

## The Big Deal:

- Good Harmonic Suppression
- Low Phase Noise
- Robust design and construction
- Small size .375" x .375" x .131"



CASE STYLE: CZ682

## Product Overview:

The MOS-1797-119+ is a Voltage Controlled Oscillator, designed to operate from 1618 to 1797 MHz for radio applications. The MOS-1797-119+ is packaged in a metal case (size of .375" x .375" x .131") to shield against unwanted signals and noise.

## Key Features

Feature	Advantages
Linear Tuning Sensitivity Ratio: 1.07:1 typ.	Optimal for loop filter design.
Good Harmonic Suppression, -20dBc typ.	Provides clear signals suitable for systems requiring high spectral purity.
Low Phase Noise: -98 dBc/Hz typ at 10kHz offset	Low phase noise improves system EVM (Error Vector Magnitude).
Good Pushing, 2 MHz/V typ.	Provides increased immunity against noisy DC lines and improves output frequency stability vs. variations in supply voltage.
Robust design and construction	Each internal component of the MOS-1797-119+ is bonded to the substrate, providing better immunity to microphonics, reduced phase hit, and decreased tombstoning risk during subsequent reflow operations.
Small size, .375" x .375 x .131"	The small size enables the MOS-1797-119+ to be used in compact designs.

# Voltage Controlled Oscillator

## MOS-1797-119+

Linear Tuning 1618 to 1797 MHz

### Features

- low phase noise, -98 dBc/Hz typ. @ 10kHz offset
- linear tuning characteristics
- low harmonics, -20 dBc typ.
- low pushing, 2 MHz/V typ.
- aqueous washable

### Applications

- wireless communications
- radio



CASE STYLE: CZ682

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)		HARMONICS (dBc)		PULLING pk-pk @12 dB Br (MHz)	PUSHING (MHz/V)	DC OPERATING POWER				
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)		SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.	Typ.	Typ.			Max.	Typ.	Max.	Vcc	Current (mA)
									Min.	Max.													
MOS-1797-119+	1618	1797	+2.5	-70	-98	-121	-141	1	4	88 - 94	20	90	-90	-20	-10	2.5	2	5	33				

### Pin Connections

RF OUT	5
VCC	3
V-TUNE	1
GROUND	2,4,6,7,8

### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	6V
All specifications	50 ohm system


Permanent damage may occur if any of these limits are exceeded.

### Tape & Reel: F60


7" Reels with 10, 20, 50, 100 devices  
13" Reels with 200, 500, 1000 devices

### Environmental Ratings: ENV65T2

### Outline Drawing



### Demo Board MCL P/N: TB-128 Suggested PCB Layout (PL-023)



### Outline Dimensions (inch/mm)







A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	wt.
.375	.375	.131	.188	.035	.033	.154	.050	.425	.183	.060	.425	.028	.154	.060	grams
9.52	9.52	3.33	4.77	0.89	0.84	3.91	1.27	10.80	4.65	1.52	10.80	0.71	3.91	1.52	.60

# Performance Data & Curves\*

# MOS-1797-119+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			I <sub>cc</sub> (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 1708 MHz (dBc/Hz)
		-40°C	+25°C	+85°C	-40°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	121.91	1490.7	1475.9	1463.0	3.04	2.46	1.30	25.49	-19.4	-35.0	-45.5	3.78	2.31	-70.55	-96.6	-117.9	-138.2	1.0	-69.75
0.50	100.38	1547.7	1534.2	1521.4	3.72	3.29	2.66	25.86	-15.6	-31.6	-44.7	4.04	1.37	-69.35	-97.7	-120.1	-140.2	3.1	-84.84
0.75	95.92	1572.5	1559.3	1547.0	3.88	3.40	2.72	25.88	-15.7	-30.7	-45.6	3.35	2.18	-70.60	-98.8	-121.0	-140.9	4.9	-90.26
1.00	92.40	1596.2	1583.3	1571.0	3.87	3.51	2.81	25.86	-15.7	-30.6	-48.0	2.86	2.91	-70.20	-98.9	-121.1	-141.2	6.2	-93.25
1.25	88.97	1618.7	1606.4	1594.4	3.74	3.33	2.75	25.89	-15.5	-29.7	-50.3	2.38	2.13	-70.30	-98.8	-121.4	-141.5	7.8	-96.06
1.50	89.47	1640.8	1628.6	1617.0	3.67	3.17	2.53	25.91	-16.2	-29.6	-54.6	2.00	1.60	-72.07	-99.6	-121.5	-141.6	10.0	-98.42
1.75	91.31	1663.4	1651.0	1639.2	3.53	3.06	2.43	25.91	-17.3	-29.8	-61.5	1.63	2.32	-72.81	-99.1	-121.5	-141.7	19.7	-106.11
2.00	92.93	1686.7	1673.8	1661.5	3.26	2.94	2.38	25.90	-19.5	-29.3	-67.7	1.27	2.15	-70.78	-98.7	-121.4	-141.7	39.4	-113.06
2.36	91.15	1720.2	1707.2	1694.1	2.80	2.64	2.28	25.91	-22.6	-29.2	-62.4	0.88	1.79	-69.75	-98.4	-121.7	-142.0	62.7	-117.48
2.50	90.07	1733.0	1720.1	1706.9	2.70	2.48	2.20	25.92	-23.9	-28.9	-59.9	0.77	2.28	-69.54	-98.5	-121.9	-142.2	79.0	-119.66
2.75	91.92	1756.1	1742.6	1729.3	2.74	2.43	2.06	25.93	-26.0	-28.1	-58.5	0.73	2.27	-70.30	-98.6	-121.1	-141.7	100.0	-121.66
3.00	92.83	1779.5	1765.6	1751.7	2.74	2.52	2.12	25.91	-27.7	-28.9	-57.5	0.80	2.05	-69.80	-97.7	-121.4	-142.1	158.5	-126.13
3.25	92.02	1802.8	1788.8	1774.7	2.70	2.51	2.18	25.91	-28.7	-30.1	-58.5	1.01	2.54	-67.76	-97.7	-121.5	-141.9	199.9	-128.23
3.50	89.78	1825.7	1811.8	1797.7	2.63	2.45	2.16	25.91	-28.7	-30.3	-58.3	1.37	2.63	-68.93	-97.8	-121.1	-141.6	252.1	-130.32
3.75	86.86	1847.9	1834.2	1820.4	2.60	2.36	2.08	25.93	-29.8	-30.8	-57.6	1.80	1.80	-68.65	-97.2	-121.2	-141.9	317.9	-132.39
4.00	86.05	1869.8	1855.9	1842.4	2.71	2.38	2.02	25.91	-31.0	-30.5	-59.2	2.35	1.89	-68.69	-97.1	-120.9	-141.4	400.9	-134.48
4.25	83.19	1891.3	1877.4	1863.9	2.69	2.47	2.10	25.90	-30.5	-30.3	-58.0	2.89	2.53	-66.94	-95.9	-120.5	-141.2	505.5	-136.58
4.50	78.41	1911.8	1898.2	1885.0	2.65	2.44	2.12	25.89	-31.3	-30.6	-58.1	3.40	2.24	-66.93	-96.3	-120.3	-141.0	637.4	-138.61
4.75	73.65	1931.2	1917.8	1905.0	2.58	2.40	2.07	25.89	-30.9	-30.6	-56.6	3.84	2.32	-66.43	-95.7	-120.3	-141.0	803.8	-140.59
5.00	67.47	1949.2	1936.3	1923.6	2.51	2.31	2.03	25.89	-30.4	-31.5	-56.3	4.16	2.78	-66.07	-96.1	-120.4	-141.0	1000.0	-141.98

\*at 25°C unless mentioned otherwise



## Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

