



Mini-Circuits

SURFACE MOUNT

Directional Coupler

RDC17-182-75+

75Ω 5 to 1800 MHz 17 dB Coupling High Isolation

KEY FEATURES

- Low Mainline Loss 0.7 dB typ.
- High Isolation, above 38 dB up to 850 MHz
- Great Coupling Flatness, ± 0.6 dB typ.



Generic photo used for illustration purposes only


APPLICATIONS

- DOCSIS® 4.0
- CATV /Broadband

PRODUCT OVERVIEW

Mini-Circuits' RDC17-182-75+ surface mount directional coupler provides 17.5 dB coupling with great flatness, low mainline loss, high isolation for 75Ω applications from 5 to 1800 MHz; This model features core and wire construction and good solderability and easy visual inspection.

FUNCTIONAL DIAGRAM



*Electrical schematic is for Directional coupler with internal transformer(s) that routes DC from all ports to ground

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		5		1800	MHz
Mainline Loss ¹ (In-Out)	5 - 1800		0.7	1.3	dB
Coupling Nominal (In-CPLF)	5 - 850		17.5 \pm 1		dB
	5 - 1800		17.5 \pm 1.5		
Coupling Flatness (\pm) (In-CPLF)	5 - 850		± 0.5	± 0.8	dB
	5 - 1800		± 0.8	± 1.2	
Isolation (Out-CPLF)	5 - 850	38	41		dB
	850 - 1800	24	31		
Return Loss (Input)	5 - 50	19	21		dB
	50 - 850	20	22		
	850 - 1800	12	17		
Return Loss (Output)	5 - 50	21	25		dB
	50 - 850	22	28		
	850 - 1800	14	20		
Return Loss (CPLF)	5 - 50	20	25		dB
	50 - 850	11	17		
	850 - 1800	10	14		

1. Mainline Loss includes coupling loss.

ABSOLUTE MAXIMUM RATINGS²

Operating Case Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Input Power	2 W

2. Permanent damage may occur if any of these limits are exceeded.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-024767
RDC17-182-75+
MCL NY
250320

PAGE 1 OF 4



SURFACE MOUNT


Directional Coupler

RDC17-182-75+


75Ω 5 to 1800 MHz 17 dB Coupling High Isolation

TYPICAL PERFORMANCE GRAPHS


INSERTION LOSS




COUPLING



ISOLATION



RETURN LOSS






SURFACE MOUNT

Directional Coupler

RDC17-182-75+

75Ω 5 to 1800 MHz 17 dB Coupling High Isolation

FUNCTIONAL DIAGRAM




*Electrical schematic is for Directional coupler with internal transformer(s) that routes DC from all ports to ground

Figure 1. RDC17-182-75+ Electrical Schematic

PAD DESCRIPTION/CONFIGURATION

Function	Pad Number	Description
Input	1	Connects to Input Port
Output	6	Connects to RF Output Port
CPL F	3	Connect to CPLF Port
Ground	2,5	Connects to Ground
CPL R	4	75 Ohm External Termination

SUGGESTED PCB LAYOUT (PL-795)




NOTES:

1. LINE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: .030±.002"; COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS LINE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Figure 2. Suggested PCB Layout PL-795

CASE STYLE DRAWING



PCB Land Pattern



SUGGESTED LAYOUT FOR PC PATTERN
TOLERANCE TO BE WITHIN ±.002

Weight: .361 grams

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.01; 3 Pl. ±.005 Inch

PRODUCT MARKING*: N/A

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

SURFACE MOUNT

Directional Coupler

RDC17-182-75+

75Ω 5 to 1800 MHz 17 dB Coupling High Isolation

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD.

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S4P Files) Data Set (.zip file) De-embedded to device pads
Case Style	TT1491-8
RoHS Status	Compliant
Tape and Reel	F34
Suggested Layout for PCB Design	PL-795
Evaluation Board	TB-RDC17-18275+ Gerber File
Environmental Rating	ENV02T1

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

