



Directional Coupler

RDC20-232-75X1+

75Ω 20 dB 5 to 2350 MHz

THE BIG DEAL

- Wideband, 5 to 2350 MHz
- Low Mainline Loss, 0.85 dB Typ. at 1800 MHz
- Good Directivity, 16 dB Typ. at 1800 MHz
- Excellent Return Loss, 26 dB Typ.
- Supports DOCSIS® 3.1/4.0 Systems
- Aqueous Washable



Generic photo used for illustration purposes only

CASE STYLE: TT2315

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- DOCSIS 3.1/4.0
- L-Band

PRODUCT OVERVIEW

Mini-Circuits' RDC20-232-75X1+ surface-mount directional coupler provides 20 dB coupling with high directivity, low mainline loss, and good return loss for 75Ω applications from 5 to 2350 MHz, supporting a variety of broadband applications including DOCSIS 3.1/4.0 systems and equipment. This model features core and wire construction with wrap-around terminations for good solderability and easy visual inspection.

KEY FEATURES

Feature	Advantages
Broadband, 5 to 2350 MHz	Supports bandwidth requirements for DOCSIS 3.1/4.0 systems and equipment.
Low Mainline Loss, 0.85 dB at 1800 MHz	Provides excellent through-path signal transmission and maintains low heat dissipation, avoiding the need for special heat sinking methods.
Power Handling, Up to 1 W	Usable in systems with a variety of signal power requirements.
Excellent Return Loss	Provides excellent matching for 75Ω systems.
Top Hat® Feature	Improves speed and accuracy of pick and place assembly.

REV. OR
NPO-002854
RDC20-232-75X1+
MCL NY
260121



ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		2350	MHz
Mainline Loss ¹	5		0.95	1.3	dB
	40		0.55	0.9	
	1218		0.65	1.0	
	1800		0.85	1.1	
	2350		1.10	1.4	
Nominal Coupling	5-1218		21±1.5		dB
	40-1800		20.5±1.0		
	40-2350		20.2±1.3		
Coupling Flatness(±)	5-1218		±1.2	±1.9	dB
	40-1800		±1.0	±2.0	
	40-2350		±1.0	±2.4	
Directivity	5	8	11		dB
	40	18	22		
	1218	15	22		
	1800	10	16		
	2350	7	12		
Return Loss (Input)	5-40	10	14		dB
	40-1800	14	26		
	1800-2350	12	20		
Return Loss (Output)	5-40	11	14		dB
	40-1800	19	24		
	1800-2350	15	22		
Return Loss (Coupled)	5-40	10	20		dB
	40-1800	12	26		
	1800-2350	10	24		
Input Power	5-2350			1	W


1. Mainline loss includes theoretical power loss at coupled port.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination




PIN CONNECTIONS

Function	Pad Number
INPUT	1
OUTPUT	6
COUPLED	3
GROUND	2
75Ω TERM EXTERNAL	4
No Internal Connection (Grounding Recommended)	5

PRODUCT MARKING: WW


DEMO BOARD MCL P/N: TB-917+ SUGGESTED PCB LAYOUT (PL-452)




NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - 0603 SIZE CHIP RESISTOR FOOT PRINT SHOWN FOR REFERENCE. FOR RESISTOR VALUE REFER TO TB-917+.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inches/mm)

A	B	C	D	E	F	G	H	J	K
.250	.280	.140	.100	.050	.040	.040	.100	.310	.050
6.35	7.11	3.56	2.54	1.27	1.02	1.02	2.54	7.87	1.27




Weight: 0.35 grams

TAPE & REEL INFORMATION: F34



TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5	0.78	22.51	12.63	14.26	14.78	15.48
10	0.61	22.13	16.96	18.04	18.71	19.06
50	0.39	21.61	25.27	25.14	26.62	25.59
100	0.35	21.46	29.03	28.09	30.33	28.41
200	0.35	21.35	32.08	30.10	33.07	29.34
400	0.39	21.21	31.60	28.99	31.52	26.42
500	0.41	21.12	31.30	28.11	30.09	25.91
1000	0.52	20.65	27.18	27.95	27.23	26.22
1200	0.56	20.48	23.96	29.58	28.41	24.47
1400	0.60	20.39	20.95	34.48	30.42	24.38
1600	0.66	20.38	18.33	58.81	37.79	26.34
2000	0.83	20.63	14.70	26.78	27.12	28.39
2350	0.98	20.80	13.88	21.01	21.68	28.61



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html