

# **MSP6TA-12+**

50Ω DC to 12 GHz 24 Volt Absorptive





CASE STYLE: HJ1143

# **The Big Deal**

- Extra long life 10 million cycles
- Low insertion loss, 0.2 dB
- High isolation, 90 dB typ.
- Absorptive
- · Reliable sleep mode switching

### **Product Overview**

Mini-Circuits' MSP6TA-12+ is an ultra-reliable, rugged-duty reflective fail-safe SP6T switch designed in break-before-make configuration offering an ultra long switching life. Powered by +24VDC, the device has a typical switching speed of 20 milliseconds, insertion loss of 0.2 dB and high isolation of 90 dB. The MSP6TA-12+ is suitable for use across a wide range of applications, including switching for automated test equipment and redundancy switching.

# **Key Features**

Feature	Advantages						
Extra long service life	Exceptionally long service life improves system reliability and reduces the need to replace switches often, making it ideal for automaticd test systems.						
High isolation, 90 dB typ.	Prevents interference from unwanted signals, ensuring signal integrity and accuracy of testing.						
Reliable sleep-mode switching	Offers dependable performance even after being set at a fixed position for prolonged periods. Highly-reliable sleep mode switching averts failures due to "wake up," making it suitable for automatic testing as well as redundancy switching applications.						
High repeatability between switching cycles	High repeatability of switching cycles ensures reliable performance critical for automated testing and other measurement applications.						

#### DC to 12 GHz 24 Volt **Absorptive**

#### **Maximum Ratings**

Operating Temperature	-15°C to +45°C
Storage Temperature	-15°C to +85°C
RF Power	20W
Control Voltage	26V

Permanent damage may occur if any of these limits are exceeded.

#### **Features**

- ultra-reliable, 10 million cycles
- low insertion loss, 0.2 dB typ.
- high isolation, 90 dB typ.
- break-before-make configuration
- · absorptive fail-safe switch
- reliable "sleep-time" switching
- protected by US Patents 5,272,458; 6,414,577; 7,633,361; 7,843,289 and 6,650,210

#### **Applications**

- (ATE) automatic test equipment
- redundancy switching for microwave radio

# MSP6TA-12+





Tight Spot SMA Wrench

From \$24.95 Click Here

back view


CASE STYLE: HJ1143


Connectors Model SMA MSP6TA-12+

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Outline Drawing**





#### Outline Dimensions (inch)

F	Е	D	С	В	Α
1.800	1.45	.63	2.00	2.10	2.63
45.72	36.83	16.00	50.80	53.34	66.80
wt		K	J	Н	G
grams		.19	.15	.172	.24
230		4.83	3.81	4.37	6.10

### Electrical Specifications at 25°C

Parameter	Condition	Min.	Typ. (Note 1)	Max.	Unit		
Frequency Range		DC	_	12	GHz		
	DC - 1 GHz	_	0.10	0.15			
Insertion Loss	1 - 6	_	0.15	0.25	dB		
insertion Loss	6 - 8	_	0.20	0.30			
	8 - 12	_	0.25	0.45			
	DC - 1 GHz	85	100	_			
Isolation	1 - 6	80	95	_	4D		
isolation	6 - 8	80	90	_	dB		
	8 - 12	80	90	_			
	DC - 1 GHz	_	1.05	1.10			
VSWR (Note 2,3)	1 - 6	_	1.20	1.25	:1		
VSWH (*******)	6 - 8	_	1.20	1.35			
	8 - 12	_	1.20	1.35			
Control Signal (Note 4)	24V	_	85	125	mA		
Switching Lifetime	0.1W	10 million	_	_	cycles		
Hot Switching	1.0W	_	1 million	_	0,000		
RF Power Cold Switching	_	_	_	20	W		

#### Notes


- 1. The performance values represents a common value for the frequency range. For typical performance across the frequency band, see performance graphs in the next page.
- 2. All ports, all states
- 3. For port IN in Energized state only.
- 4. +24 Volt applied to energized port, COM is negative.

Additional Spe	cifications
Operating Voltage Range	24V (nom) ±1V
Switching Time (Typ.)	20ms


### **Marking Drawing**





### **Switching Position (Non-Energized)**



FREQ. (MHz)		ON INSERTION LOSS (dB)					ISOLATION (dB)			VSWR				
	IN-J1	IN-J2	IN-J3	IN-J4	IN-J5	IN-J6		IN	J1-ON	J2-ON	J3-ON	J4-ON	J5-ON	J6-ON
1000	0.04	0.04	0.04	0.04	0.04	0.04	99.41	1.03	1.03	1.03	1.04	1.05	1.04	1.04
1800 2500	0.06 0.07	0.06 0.07	0.06 0.07	0.06 0.07	0.06 0.06	0.06 0.06	108.37 113.94	1.04 1.03	1.04 1.04	1.05 1.04	1.05 1.05	1.07 1.07	1.05 1.05	1.05 1.06
3800	0.07	0.09	0.07	0.07	0.07	0.07	112.01	1.02	1.02	1.01	1.02	1.04	1.03	1.03
4550	0.10	0.09	0.09	0.09	0.08	0.08	105.44	1.02	1.02	1.01	1.02	1.04	1.03	1.03
5500	0.10	0.10	0.10	0.09	0.10	0.10	118.76	1.05	1.03	1.05	1.05	1.08	1.05	1.06
6000	0.11	0.11	0.10	0.10	0.11	0.10	109.45	1.07	1.06	1.07	1.07	1.11	1.08	1.09
7000	0.13	0.13	0.13	0.13	0.12	0.12	102.15	1.13	1.11	1.13	1.13	1.18	1.13	1.14
7500	0.14	0.14	0.14	0.14	0.13	0.13	96.47	1.15	1.13	1.15	1.16	1.20	1.15	1.16
9000	0.16	0.15	0.16	0.16	0.15	0.15	101.34	1.15	1.15	1.14	1.18	1.21	1.17	1.19
10000	0.16	0.15	0.16	0.15	0.16	0.16	93.14	1.13	1.14	1.11	1.16	1.18	1.16	1.18
11000	0.16	0.16	0.16	0.15	0.15	0.15	91.84	1.10	1.11	1.06	1.11	1.14	1.14	1.14
12000	0.16	0.16	0.16	0.14	0.15	0.15	95.49	1.04	1.05	1.00	1.05	1.05	1.08	1.06
13005	0.18	0.19	0.18	0.15	0.16	0.17	92.38	1.05	1.06	1.09	1.09	1.08	1.05	1.08
15000	0.32	0.33	0.32	0.26	0.27	0.27	99.05	1.39	1.38	1.46	1.38	1.33	1.35	1.34







#### **Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

