

Coaxial High Pass Filter

50Ω 780 to 3000 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- rugged shielded case
- other standard and custom NHP models available with wide selection of fco

Applications

- lab use
- transmitters/receivers
- radio communications

NHP-800+
NHP-800



CASE STYLE: FF57

Connectors	Model	Price	Qty.
N-Type	NHP-800(+)	\$39.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

High Pass Filter Electrical Specifications

STOPBAND (MHz)		fco (MHz) Nom.	PASSBAND (MHz)	VSWR (:1)	
(loss > 40 dB)	(loss > 20 dB)	(loss 3 dB)	(loss <1 dB)	Stopband Typ.	Passband Typ.
DC-445	445-570	710	780-3000	17	2.1


Outline Drawing




Outline Dimensions (inch mm)

B	D	E	wt
.67	2.90	.82	grams
17.02	73.66	20.83	90.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) $\bar{x}$	Insertion Loss (dB) σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
10.00	74.59	6.84	0.07	200.00	0.49
100.00	94.26	7.80	0.06	300.00	0.44
200.00	80.68	1.20	0.07	400.00	0.81
300.00	68.07	0.23	0.10	485.00	0.90
400.00	54.92	0.50	0.14	490.00	0.92
485.00	41.80	0.71	0.21	495.00	0.95
490.00	41.00	0.71	0.21	500.00	0.95
495.00	40.19	0.72	0.22	550.00	1.10
500.00	39.38	0.73	0.22	600.00	1.42
550.00	31.17	0.81	0.32	610.00	1.50
600.00	22.58	0.88	0.41	620.00	1.59
620.00	19.06	0.91	0.51	625.00	1.64
650.00	13.62	0.95	0.77	650.00	2.05
660.00	11.79	0.95	0.91	660.00	2.29
670.00	9.98	0.94	1.13	670.00	2.55
700.00	5.03	0.77	2.65	700.00	3.46
710.00	3.71	0.66	3.62	710.00	3.77
750.00	1.03	0.15	13.50	750.00	3.59
800.00	0.67	0.03	19.87	800.00	2.37
965.00	0.44	0.01	28.39	965.00	1.30
1070.00	0.41	0.00	39.79	1070.00	1.04
1180.00	0.40	0.00	33.07	1180.00	0.87
1290.00	0.40	0.01	25.70	1290.00	0.75
1400.00	0.42	0.02	21.82	1400.00	0.67
1460.00	0.43	0.02	20.66	1460.00	0.63
1570.00	0.46	0.03	19.47	1570.00	0.58
1680.00	0.48	0.03	19.23	1680.00	0.54
1790.00	0.48	0.04	19.63	1790.00	0.50
2000.00	0.49	0.04	21.39	2000.00	0.46
3000.00	0.57	0.03	18.79	3000.00	0.37



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

ALL NEW
minicircuits.com

REV. B
M108326
NHP-800
070131