

# Plug-In Attenuator/Switch

## PAS-2+

50Ω Bi-Phase 10 to 1000 MHz



Generic photo used for illustration purposes only

CASE STYLE: A01

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Control Current	30mA
Permanent damage may occur if any of these limits are exceeded.	

### Pin Connections

INPUT	1
OUTPUT	8
CONTROL	3,4^
GROUND	2,5,6,7
CASE GROUND	2,5,6,7

^ pins must be connected together externally

### Outline Drawing



### Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

### Features

- wideband, 10 to 1000 MHz
- hermetic case
- high in-out isolation
- excellent amplitude and phase unbalance

### Applications


- bi-phase modulator
- electronic attenuator
- military hi-rel applications

### Attenuator/Switch Electrical Specifications


FREQUENCY (MHz)	INSERTION LOSS (dB) ±20 mA	MAX. INPUT PWR (dBm) ±20 mA	IN-OUT ISOLATION (dB) 0 mA			BI-PHASE X̄ (±20 mA) Typ.	
			L	M	U	Δ AMP (dB)	Phase (deg.) deviation from 180°
10-1000	DC-0.05	20 29	50 40 30	40 30 25	35 25	m	Total Range
			Typ. Min.	Typ. Min.	Typ. Min.	m	Total Range

L = low range [ $f_L$  to  $10 f_L$ ] M = mid range [ $10 f_L$  to  $f_U/2$ ] U = upper range [ $f_U/2$  to  $f_U$ ] m = [ $2 f_L$  to  $f_U/2$ ]  
Performance specifications apply for input power up to 10 dB below stated 1 dB compression.

### suggested control port biasing configuration






### electrical schematic



### Typical Performance Data

Freq. (MHz)	I. Loss (dB) at 20mA	±Control ΔAMP (dB)		20mA ΔPhase (deg.)	Isolation (dB) (in-out) (in-con)		Input R. Loss (dB)	Control Current (mA)	Attenuation (dB)			Phase Δ ref at 15mA Ctrl			Input VSWR		
		x	σ		x	x			x	x	10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz	10 MHz
10.0	3.50	0.025	0.01	180.00	70	47	12.3	0.0000	71.8	43.8	38.2	-37.1	96.0	63.6	3.6	2.9	7.5
19.9	3.52	0.015	0.01	180.00	68	40	12.7	0.0003	63.7	44.2	38.1	-34.3	93.2	62.4	3.6	2.9	7.5
39.7	3.61	0.008	0.01	179.90	67	35	12.6	0.0004	55.7	43.8	38.1	-12.5	86.0	57.8	3.6	2.9	7.5
59.5	3.63	0.006	0.01	179.90	65	31	12.5	0.0016	51.2	43.3	38.1	-8.5	80.1	52.8	3.6	2.8	7.4
79.3	3.66	0.006	0.01	179.90	64	29	12.5	0.0057	45.4	41.1	36.8	-4.6	55.5	35.7	3.6	2.8	7.3
86.7	3.68	0.006	0.01	179.90	63	28	12.5	0.0105	41.5	38.6	35.6	-1.2	42.6	23.4	3.5	2.8	7.1
99.1	3.73	0.006	0.01	179.90	62	27	12.4	0.0161	38.3	36.0	33.7	1.5	34.4	12.9	3.5	2.8	6.9
163.5	3.95	0.006	0.01	179.80	58	23	12.3	0.0286	33.9	31.8	30.1	3.6	24.5	0.6	3.4	2.7	6.6
237.7	4.03	0.007	0.01	179.70	55	20	12.1	0.0437	30.3	28.4	27.1	4.3	20.7	-5.6	3.3	2.6	6.2
314.4	4.05	0.008	0.01	179.37	52	18	12.0	0.0734	26.2	24.4	23.2	5.1	16.3	-9.9	3.1	2.4	5.6
391.2	4.23	0.012	0.02	179.60	50	17	12.1	0.1029	23.6	21.8	20.8	5.0	14.4	-11.4	2.9	2.3	5.2
467.9	4.36	0.017	0.04	179.60	48	17	12.3	0.1510	20.7	19.1	18.2	5.0	12.8	-11.9	2.7	2.1	4.7
500.1	4.38	0.021	0.04	179.60	47	17	12.4	0.2540	17.1	15.6	15.1	4.6	10.4	-11.1	2.4	1.8	4.0
542.1	4.48	0.027	0.06	179.50	46	17	12.5	0.3743	14.6	13.3	13.1	4.3	9.0	-9.9	2.1	1.6	3.6
618.9	4.63	0.040	0.10	179.50	44	18	12.6	0.6438	11.5	10.6	10.8	3.5	6.9	-7.5	1.7	1.3	3.1
695.6	4.90	0.053	0.13	179.60	43	20	12.1	0.9350	9.7	9.1	9.6	3.0	5.4	-6.0	1.5	1.2	2.9
772.3	5.02	0.064	0.16	179.38	41	23	10.8	1.7496	7.2	7.2	8.2	2.0	3.6	-3.6	1.2	1.1	2.7
846.6	5.51	0.073	0.16	179.70	41	21	9.1	2.6537	5.5	5.9	7.3	1.3	1.9	-1.8	1.2	1.3	2.7
923.3	6.21	0.087	0.21	179.80	40	17	7.5	7.3045	4.3	4.9	6.7	0.5	0.6	-0.7	1.4	1.5	2.6
1000.0	7.06	0.093	0.36	180.40	40	14	6.3	15.1437	3.6	4.5	6.4	0.1	0.1	-0.1	1.5	1.6	2.6



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C  
M151107  
PAS-2+  
WP/TD/CP/AM  
200401