

50Ω 41 to 200 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT 1

OUTPUT 8

GROUND 2,3,4,5,6,7

CASE GROUND 2,3,4,5,6,7

Features

- rugged shielded case, hermetically sealed
- other standard and custom PHP models available with wide selection of fco

Applications

- lab use
- transmitters/receivers
- military/hi-rel application



Generic photo used for illustration purposes only


CASE STYLE: A01

+RoHS Compliant



The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

High Pass Filter Electrical Specifications



STOPBAND (MHz)		fco (MHz) Nom.	PASSBAND (MHz)	VSWR (:1)	
(loss > 40 dB)	(loss > 20 dB)	(loss 3 dB)	(loss <1 dB)	Stopband Typ.	Passband Typ.
DC-20	20-26	37	41-200	17	1.5

Outline Drawing**Outline Dimensions (inch/mm)**

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

typical frequency response**electrical schematic****Typical Performance Data**

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
$\bar{x}$	σ			
1.00	67.35	2.1	17.00	3.77
3.00	69.22	2.0	18.00	4.22
7.00	67.66	1.8	19.00	4.55
11.00	69.57	1.3	20.00	4.91
14.00	78.81	9.5	21.00	9.75
15.00	74.91	4.7	22.00	12.75
17.00	62.53	1.4	22.50	24.54
18.00	59.52	3.2	23.00	0.69
19.00	54.95	1.7	23.50	23.43
20.00	51.14	1.0	24.00	13.44
21.00	47.48	1.0	25.00	16.30
22.50	42.82	0.7	26.00	17.22
23.50	39.50	0.6	28.00	19.35
24.00	38.04	0.5	29.00	21.30
25.00	34.89	0.6	30.00	23.37
26.00	31.98	0.5	32.00	29.87
28.00	26.15	0.5	34.00	39.03
30.00	20.49	0.5	36.00	49.41
34.00	9.52	0.4	36.50	51.69
36.00	4.92	0.2	37.00	52.35
36.50	4.01	0.2	38.00	52.06
37.00	3.25	0.2	39.00	47.84
38.00	2.07	0.1	41.00	37.11
39.00	1.37	0.1	120.50	3.01
41.00	0.81	0.1	133.50	2.11
133.50	0.19	0.1	147.00	2.07
160.00	0.16	0.1	160.00	1.41
173.50	0.16	0.1	173.50	1.04
186.50	0.16	0.1	186.50	1.54
200.00	0.16	0.1	200.00	1.27

**Notes**

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

