

Engineering Development Model

Voltage Controlled Oscillator ROS-ED11626C/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : CK605

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	99		101	MHz
Tuning Voltage	1		9	V
Power Output		10		dBm
Phase Noise				
at 1 kHz offset		-102		dBc/Hz
at 10 KHz offset		-127		dBc/Hz
at 100 KHz offset		-147		dBc/Hz
at 1000 kHz offset		-167		dBc/Hz
Pulling at 12 dBm PK-PK all phases		0.128		MHz
Pushing at Vcc ± 5%		0.13		MHz/V
Tuning Sensitivity		2.5-3.0		MHz/V
Harmonic Suppression		-22		dBc
3 dB Modulation Bandwidth		10,000		kHz
Supply Voltage		10		V
Supply Current			20	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+12V
Absolute Tuning Voltage (Vtune)	+11V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16