

Engineering Development Model


Voltage Controlled Oscillator

POS-ED5634B/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : A06

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	450		1152	MHz
Tuning Voltage	0.3		19	V
Power Output		+7		dBm
Phase Noise				
at 1 kHz offset		-73		dBc/Hz
at 10 KHz offset		-93		dBc/Hz
at 100 KHz offset		-113		dBc/Hz
at 1000 kHz offset		-133		dBc/Hz
Pulling at 12 dBm PK-PK all phases		6		MHz
Pushing at Vcc=5V±0.25V		1.5		MHz/V
Tuning Sensitivity		30 - 42		MHz/V
Harmonic Suppression		-26		dBc
3 dB Modulation Bandwidth		100		kHz
Supply Voltage		12		V
Supply Current			20	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+14V
Absolute Tuning Voltage (Vtune)	+21V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	8
GROUND	3,4,5,6,7