

Engineering Development Model


Voltage Controlled Oscillator

POS-ED6986/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : A06

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	950		1750	MHz
Tuning Voltage	0.5		20	V
Power Output		+7		dBm
Phase Noise				
at 1 kHz offset		-73		dBc/Hz
at 10 KHz offset		-96		dBc/Hz
at 100 KHz offset		-115		dBc/Hz
at 1000 kHz offset		-134		dBc/Hz
Pulling at 12 dBm PK-PK all phases		15		MHz
Pushing at Vcc=5V±0.25V		2.8		MHz/V
Tuning Sensitivity		20 - 65		MHz/V
Harmonic Suppression		-11		dBc
3 dB Modulation Bandwidth		5000		kHz
Supply Voltage		12		V
Supply Current			28	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+14V
Absolute Tuning Voltage (Vtune)	+22V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	8
GROUND	3,4,5,6,7