

Engineering Development Model


Voltage Controlled Oscillator

POS-ED7899/6

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : C145

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	228		315	MHz
Tuning Voltage	1		20	V
Power Output		+8.5		dBm
Phase Noise				
at 1 kHz offset		-102		dBc/Hz
at 10 KHz offset		-121		dBc/Hz
at 100 KHz offset		-141		dBc/Hz
at 1000 kHz offset		-160		dBc/Hz
Pulling at 12 dBm PK-PK all phases		0.5		MHz
Pushing at Vcc=5V±0.25V		0.15		MHz/V
Tuning Sensitivity		2 - 7		MHz/V
Harmonic Suppression		-36		dBc
3 dB Modulation Bandwidth		2600		kHz
Supply Voltage		12		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+14V
Absolute Tuning Voltage (Vtune)	+22V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	14
GROUND	1,2,3,4,9,12,15,16