


Engineering Development Model

Voltage Controlled Oscillator

ROS-ED12037/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : CK1113

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	2130		2135	MHz
Tuning Voltage	0.2		4.8	V
Power Output		+7		dBm
Phase Noise				
at 1 kHz offset		-96		dBc/Hz
at 10 KHz offset		-121		dBc/Hz
at 100 KHz offset		-141		dBc/Hz
at 1000 kHz offset		-161		dBc/Hz
Pulling at 12 dBr PK-PK all phases		0.2		MHz
Pushing at Vcc=5V±0.25V		0.2		MHz/V
Tuning Sensitivity		5 - 6		MHz/V
Harmonic Suppression		-15		dBc
3 dB Modulation Bandwidth		270000		kHz
Supply Voltage		6		V
Supply Current			40	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+8V
Absolute Tuning Voltage (Vtune)	+6.8V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16