

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED12617/4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DV874

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	470		520	MHz
Tuning Voltage	.5		4.7	V
Power Output		0		dBm
Phase Noise	at 1 kHz offset	-89		dBc/Hz
	at 10 KHz offset	-114		dBc/Hz
	at 100 KHz offset	-134		dBc/Hz
	at 1000 kHz offset	-154		dBc/Hz
Pulling at 12 dB _r PK-PK all phases		.35		MHz
Pushing at V _{cc} ± 5%		.7		MHz/V
Tuning Sensitivity		15-19		MHz/V
Harmonic Suppression		-17		dBc
3 dB Modulation Bandwidth		90,000		kHz
Supply Voltage		5		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (V _{cc})	+7V
Absolute Tuning Voltage (V _{tune})	+6.7V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
MODULATION	6
GROUND	1,3,4,5,7,8,9,11,12,13,15,16



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

RF/RF MICROWAVE COMPONENTS



REV. X2
ROS-ED12617/4
12/17/2008
Page 1 of 1