2 Way-90° Power Splitter

3100 to 5900 MHz



CASE STYLE: GE0805C-1

The Big Deal

- •High Power handling (8W)
- •Low Unbalance, 0.5 dB & 2 deg. typ.
- •Industry leading combination of size/bandwidth

Product Overview

Mini-Circuits new 90° Power Splitter, model: QCS-592+, offers an industry leading combination of operating bandwidth and size; supporting nearly an octave band in a miniature EIA-0805 form factor. The outstanding phase and amplitude unbalance make this component a versatile building block for use in a variety of systems and sub-system designs.

Key Features

| Feature | Advantages |
|-----------------------------------|---|
| Small Size | Offered in the EIA-0805 package size, the QCS-592+ offers an industry leading combination of size, bandwidth and frequency. The small footprint (2.0mm x1.25mm) allows for reduced parasitics in systems with improved performance and simplified layout. |
| Low Phase and Amplitude Unbalance | Supporting 2 deg. and 0.5 dB unbalance make this 90° hybrid applicable for use in higher level integrated components such as image reject mixers, single sideband modulators, phase shifters, variable attenuators, and balance amplifiers. |
| High Power Handling | Capable of operating up to 8W, the LTCC construction of the QCS-592+ makes this 90° hybrid a robust, rugged product that can be used effectively in either the transmit or receive paths. |

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

Power Splitter/Combiner

QCS-592+

Generic photo used for illustration purposes only

CASE STYLE: GE0805C-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site

Available Tape and Reel at no extra cost

20, 50, 100, 200, 500,1000, 2000

for RoHS Compliance methodologies and qualifications

Devices/Reel

Reel Size

0.5

0.5

0.5

0.5

0.8

0.9

0.9

0.9

0.7

1.1

dΒ

2 Way-90°

 50Ω

3100 to 5900 MHz

Maximum Ratings


| Operating Temperature | -55°C to 100°C |
|-----------------------------|----------------|
| Storage Temperature | -55°C to 100°C |
| Power Input (as a splitter) | 15W* max. |
| | |

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

| SUM PORT | 1 |
|----------------------|-----|
| PORT 1 (0°) | 4 |
| PORT 2 (+90°) | 6 |
| GROUND | 2,5 |
| 50 OHM TERM EXTERNAL | 3 |
| | |


Outline Drawing



Outline Dimensions (inch)

| Α | В | С | D | Е | F |
|-----------|-----------|-----------|-----------|------|-------------|
| .079 | .049 | .033 | .014 | .012 | .012 |
| 2.01 | 1.24 | 0.84 | 0.36 | 0.30 | 0.30 |
| | | | | | |
| G | Н | J | K | | wt |
| G .026 | H .014 | J .039 | K .110 | | wt grams |

Electrical Schematic



Features

- · Low insertion loss, 0.6 dB typ.
- · High isolation, 23 dB typ.
- Miniature size, 0.079"x0.049"x0.033"
- LTCC construction
- High power

Applications

Balanced amplifiers

Amplitude Unbalance

VSWR

- Modulators
- WiMax
- Phase Shifter
- Attenuator

| WiFi ISM Electrical Specifications at 25°C | | | | | | | |
|--|--|----------------------------------|--|--|--------|--|--|
| Parameter | Frequency (MHz) | Min. | Тур. | Max. | Unit | | |
| Frequency | | 3100 | | 5900 | MHz | | |
| Insertion Loss (Avg. Of Coupled Outputs) above 3 dB | 3100-3300 3300-3600 3600-3900 3900-5100 5100-5700 5700-5900 | | 0.5 0.5 0.5 0.5 0.5 0.7 | 0.7 0.7 0.7 0.7 0.8 1.0 | dB | | |
| Isolation | 3100-3300 3300-3600 3600-3900 3900-5100 5100-5700 5700-5900 | 19 20 18 17 16 16 | 25 28 27 24 24 23 | | dB | | |
| Phase Unbalance | 3100-3300 3300-3600 3600-3900 3900-5100 5100-5700 5700-5900 | | 2.0 2.0 2.0 2.0 2.0 2.0 | 5.0 5.0 5.0 5.0 5.0 5.0 | Degree | | |
| | 3100-3300 | | 1.0 | 1.4 | | | |

Demo Board MCL P/N: TB-489-592+ Suggested PCB Layout (PL-304)

3300-3600


3600-3900

3900-5100

5100-5700

5700-5900

3100-5900



- 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001"; COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Typical Performance Data

| Frequency (MHz) | Total Loss¹ (dB) | | Amplitude Unbalance (dB) | Isolation (dB) | Phase Unbalance (deg.) | VSWR S | VSWR 1 | VSWR 2 |
|--------------------|---------------------|------|--------------------------------|-------------------|------------------------------|-----------|-----------|-----------|
| | S-1 | S-2 | | | | | | |
| 3100.00 | 3.94 | 2.91 | 1.03 | 24.79 | 92.28 | 1.11 | 1.36 | 1.12 |
| 3250.00 | 3.79 | 3.03 | 0.76 | 26.60 | 92.31 | 1.13 | 1.32 | 1.14 |
| 3300.00 | 3.76 | 3.08 | 0.68 | 27.14 | 92.30 | 1.14 | 1.31 | 1.14 |
| 3350.00 | 3.71 | 3.11 | 0.60 | 27.75 | 92.28 | 1.15 | 1.30 | 1.14 |
| 3800.00 | 3.45 | 3.45 | 0.00 | 28.33 | 92.03 | 1.18 | 1.24 | 1.16 |
| 3900.00 | 3.41 | 3.51 | 0.11 | 27.56 | 92.00 | 1.18 | 1.23 | 1.16 |
| 4400.00 | 3.33 | 3.68 | 0.35 | 24.67 | 92.13 | 1.14 | 1.22 | 1.12 |
| 4475.00 | 3.33 | 3.68 | 0.36 | 24.49 | 92.19 | 1.14 | 1.22 | 1.10 |
| 4500.00 | 3.33 | 3.68 | 0.35 | 24.46 | 92.20 | 1.14 | 1.22 | 1.10 |
| 4550.00 | 3.34 | 3.69 | 0.35 | 24.26 | 92.24 | 1.13 | 1.22 | 1.09 |
| 4975.00 | 3.41 | 3.63 | 0.22 | 24.20 | 92.75 | 1.13 | 1.15 | 1.12 |
| 5000.00 | 3.41 | 3.62 | 0.21 | 24.16 | 92.77 | 1.13 | 1.14 | 1.13 |
| 5050.00 | 3.42 | 3.61 | 0.19 | 24.28 | 92.84 | 1.14 | 1.13 | 1.14 |
| 5500.00 | 3.61 | 3.61 | 0.00 | 24.15 | 92.73 | 1.24 | 1.04 | 1.28 |
| 5900.00 | 3.96 | 3.58 | 0.37 | 22.06 | 92.29 | 1.38 | 1.25 | 1.42 |

^{1.} Total Loss = Insertion Loss + 3dB splitter loss.







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp