

Engineering Development Model

Power Splitter/Combiner RACK-2-ED11006A/2

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-949

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1500		2650 MHz
Isolation	1500 - 2650 MHz		23	dB
Insertion Loss Above 3.0 dB	1500 - 2650 MHz		0.31	dB
Phase Unbalance	1500 - 2650 MHz		0.72	deg.
Amplitude Unbalance	1500 - 2650 MHz		0.06	dB
VSWR	SUM Port		1.16	(:1)
	OUT Ports		1.10	(:1)

MAXIMUM RATINGS	
Operating Temperature	-5°C to 85°C
Storage Temperature	-40°C to 85°C

PIN CONNECTIONS	
SUM PORT	J1, DIN 1.0/2.3, JACK
PORT 1	J2, SMA, PLUG
PORT 2	J3, SMA, PLUG

Functional Diagram

