

Engineering Development Model

Power Splitter/Combiner RACK-2-ED13461/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE: 99-01-1340

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		550		1500 MHz
Isolation	550-1500 MHz		5.80	
Insertion Loss Above 3.0 dB	550-1500 MHz		0.25	
Phase Unbalance	550-1500 MHz		0.55	
Amplitude Unbalance	550-1500 MHz		0.07	
VSWR	SUM Port		1.29	(:1)
	OUT Ports		2.84	(:1)

MAXIMUM RATINGS	
Operating Temperature	-5°C to 85°C
Storage Temperature	-40°C to 85°C

COAXIAL CONNECTIONS	
SUM PORT	J1, N-TYPE, JACK
PORT 1	J2, SMA, PLUG
PORT 2	J3, SMA, PLUG

Functional Diagram

