

Engineering Development Model

Power Splitter/Combiner RACK-2-ED13462/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE: 99-01-1341

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		500		1210 MHz
Isolation	500-1210 MHz		22	dB
Insertion Loss Above 3.0 dB	500-1210 MHz		0.30	dB
Phase Unbalance	500-1210 MHz		0.15	deg.
Amplitude Unbalance	500-1210 MHz		0.01	dB
VSWR	SUM Port		1.27	(:1)
	OUT Ports		1.11	(:1)

MAXIMUM RATINGS	
Operating Temperature	-5°C to 85°C
Storage Temperature	-40°C to 85°C

COAXIAL CONNECTIONS	
SUM PORT	J1, DIN 1.0/2.3, JACK
PORT 1	J2, SMA, PLUG
PORT 2	J3, SMA, PLUG

Functional Diagram

