


Engineering Development Model

Voltage Controlled Oscillator

ROS-ED12999/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK605

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	4422		4426	MHz
Tuning Voltage		1 - 5		V
Power Output		+7		dBm
Phase Noise				
at 1 kHz offset		-75		dBc/Hz
at 10 KHz offset		-98		dBc/Hz
at 100 KHz offset		-118		dBc/Hz
at 1000 kHz offset		-138		dBc/Hz
Pulling at 12 dB PK-PK all phases		5		MHz
Pushing at Vcc=5V±0.25V		2.5		MHz/V
Tuning Sensitivity		22 - 24		MHz/V
Harmonic Suppression		-35		dBc
3 dB Modulation Bandwidth		230000		kHz
Supply Voltage		5		V
Supply Current			50	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7V
Absolute Tuning Voltage (Vtune)	+7V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16