

Engineering Development Model

Power Splitter/Combiner RACK-2-ED9940C/2

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-939

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1800		2150 MHz
Isolation	1800 - 2150 MHz		6	dB
Insertion Loss Above 3.0 dB	1800 - 2150 MHz		0.20	dB
Phase Unbalance	1800 - 2150 MHz		0.12	deg.
Amplitude Unbalance	1800 - 2150 MHz		0.08	dB
VSWR	SUM Port		1.10	(:1)
	OUT Ports		3.00	(:1)

MAXIMUM RATINGS	
Operating Temperature	-5°C to 85°C
Storage Temperature	-40°C to 85°C

PIN CONNECTIONS	
SUM PORT	J1, N-TYPE, JACK
PORT 1	J3, SMA, PLUG
PORT 2	J4, SMA, PLUG

Functional Diagram

