# Surface Mount **Bandpass Filter**

**RBP-140+** 

 $50\Omega$ 130 to 150 MHz

# **The Big Deal**

- Good VSWR, 1.35:1 typical
- High rejection, 40 dB typical
- Linear phase
- Symmetrical band pass response
- Small size 0.35" x 0.35" x 0.10"



Generic photo used for illustration purposes only CASE STYLE: GP731

### **Product Overview**

The RBP-140+ is a narrow-band bandpass filter in a small shielded package (size of 0.35" x 0.35" x .10") fabricated using SMT technology. The RBP-140+ offers a symmetrical bandpass and linear phase characteristics. In addition it has repeatable performance across production lots and consistent performance across temperature.

# **Key Features**

Feature	Advantages
Small size, 0.35" x 0.35" x 0.10"	The unique surface mount package enables the RBP-140+ to be used in compact designs.
More than 40 dB rejection up to 3000MHz	This enables the filter to attenuate spurious signals and reject harmonics for broad band of frequency.
Symmetrical band pass response	Uniform passband insertion loss.
Minimal phase deviation over attenuation range, ± 7deg typical at Fc ±15 MHz	Can provide low signal distortion over the attenuation range
Good VSWR, 1.35:1 typical in Passband	The RBP-140+ has very good return loss for a narrow bandwidth which provides good matching when used with other devices.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/WCLStore/terms.jsp

# Surface Mount **Bandpass Filter**

130 to 150 MHz  $50\Omega$ 

## RBP-140+



Generic photo used for illustration purposes only CASE STYLE: GP731

13

±9

:1

deg


## **Features**

- · High rejection, 40dB typical
- Linear phase, up to ±7deg typical over Fc ±15MHz
- · Good VSWR, 1.35:1 typical in passband
- Small size 0.35" x 0.35" x 0.1"
- · Shielded case
- Aqueous washable


#### **Applications**

- Mobile application
- · Space research
- · Defence system
- Satellite

### **Functional Schematic**



#### **Typical Frequency Response**



#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### Frequency (MHz) **Parameter** Тур. Max. Unit Center Frequency MHz Fc 140 **Pass Band** Insertion Loss F1-F2 130-150 2.6 3.5 dΒ 130-150 **VSWR** F1-F2 1.35 1.7 :1 Insertion Loss DC-F3 DC-100 20 29 dB Stop Band, Lower **VSWR** DC-F3 DC-100 25 :1 Insertion Loss F4-F5 178-3000 20 27 dB Stop Band, Upper

178-3000

125-155

F4-F5

Fc ±15MHz

Electrical Specifications at 25°C

Maximum Ratings			
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power Input	0.3W max.		


**VSWR** 


Permanent damage may occur if any of these limits are exceeded.


**Maximum Deviation from Linear Phase** 


### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg)
1	81.53	7360.92	125.00	3.42
60	44.27	579.06	126.00	2.16
100	29.51	31.03	128.00	0.35
109	15.66	10.56	130.00	-0.73
114	8.73	4.20	132.00	-1.24
120	3.83	1.44	134.24	-0.97
125	2.66	1.16	134.44	-0.93
130	2.31	1.22	136.24	-0.62
140	2.23	1.34	138.24	-0.12
150	2.57	1.11	140.00	0.29
161	5.47	2.56	142.24	0.96
166	10.71	6.05	144.24	1.24
178	28.39	22.29	146.04	1.21
180	31.55	25.19	146.84	1.11
182	34.88	28.03	147.04	1.08
190	52.41	40.41	148.00	0.54
200	46.17	57.91	150.00	-0.30
600	85.00	289.53	151.00	-0.91
2200	65.48	31.60	153.00	-2.68
3000	55.39	26.33	155.00	-5.42









- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


  C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

**RBP-140+ Bandpass Filter** 

#### **Pad Connections**

INPUT	2
OUTPUT	6
GROUND	1,3,4,5,7,8

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)




NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### **Outline Drawing**



#### **PCB Land Pattern**



Suggested Layout, Tolerance to be within ±.002

### Outline Dimensions ( inch )

A .350 8.89	.350 8.89	.100 2.54	D .175 4.45	E .075 1.91	F .100 2.54	G .110 2.79	H .040 1.02	J .080 2.03
K .050	.040	M .195	N .390	P .120	Q .390	R .070		wt grams
1.27	1.02	4.95	9.91	3.05	9.91	1.78		0.25

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

