

# RF Switch Matrix

RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female

#### THE BIG DEAL

- Eight independent mechanical SPDT switches
- 20W power rating (cold switching)
- High isolation, 85 dB typ
- · High reliability



CASE STYLE: LM1852



DOWNLOAD SOFTWARE PACKAGE

### RoHS Compliant See our website for RoHS Compliance methodologies and qualifications

#### **APPLICATIONS**

- Fail safe / redundancy switching
- Automated test equipment
- Satcom switching

#### **PRODUCT OVERVIEW**

Mini-Circuits' RC-8SPDT-A18 contains eight independently controlled, electro mechanical SPDT switches. Each switch operates over an extremely wide bandwidth, from DC to 18 GHz with high isolation and low insertion loss. The absorptive switches are of a failsafe and break before make configuration, with a lifetime of 5 million switching cycles per switch when used within the noted specifications.

The switch box is constructed in a compact, rugged metal case (4.5 x 12.0 x 2.25") with all SMA (f) RF connectors on the front panel. The switches are controlled via USB or Ethernet, allowing control directly from a PC, or remotely over a network. Full software support is provided, including our user friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32 bit and 64 bit systems). Download the software from our website at <a href="https://www.minicircuits.com/softwaredownload/rfswitchcontroller.html">www.minicircuits.com/softwaredownload/rfswitchcontroller.html</a>.

#### **KEY FEATURES**

Feature	Advantages	
Eight mechanical SPDTswitches	Mechanical absorptive switches provide high reliability, repeatable high performance and internal termination of input signals on the disconnected paths	
High power operation from DC to 18 GHz	Supports a wide range of RF test and signal routing applications up to X and Ku bands, with 40W input power.	
Break-before make configuration	Prevents a momentary connection of the old and new signal paths, reducing the inconsistent transient effects that could otherwise be observed during switching	
USB & Ethernet control	USB HID and Ethernet (HTTP / Telnet) interfaces provide easy compatibility with a wide range of software setups and programming environments	
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments	

REV. F ECO-021362 EDR-10927/10F1 RC-8SPDT-A18 MCL NY 240401





### **USB & ETHERNET CONTROLLED** RF Switch Matrix

### RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female

#### **ELECTRICAL SPECIFICATIONS**

Parameter	Conditions (GHz)	Min.	Тур.	Max.	Units	
Frequency	_	DC		18	GHz	
	DC to 1 GHz	-	0.10	0.15		
DE leasaities Langue (ann accitate)	1 to 8 GHz	_	0.15	0.30	dB	
RF Insertion Loss (per switch)	8 to 12 GHz	_	0.25	0.40		
	12 to 18 GHz	-	0.30	0.50		
	DC to 1 GHz	-	1.05	-		
RF VSWR	1 to 8 GHz	_	1.20	_	.1	
RF VSVVR	8 to 12 GHz	_	1.20	_	:1	
	12 to 18 GHz	_	1.25	_		
	DC to 1 GHz	85	100	-		
DE la clatica (com avritale)	1 to 8 GHz	75	90	_	dD.	
RF Isolation (per switch)	8 to 12 GHz	70	80	_	dB	
	12 to 18 GHz	60	66	_		
Switching Time	-	-	15	-	ms	
RF Power (cold switching) <sup>1</sup>	-	-	-	40	W	
Rated Voltage	24V input LISP port	23	24	25	V	
	24V <sub>DC</sub> input USB port	-	5	_		
Rated Current (24V <sub>DC</sub> input)	All switches in COM -> 2 position	-	790	1055		
	All switches in COM -> 1 position	-	115	165	mA	
Rated Current (USB port)		-	10	20		
Life (or an arritab)	@ 100 mW (hot switching) <sup>2</sup>	-	5	-	million	
Life (per switch)	@ 1 W (hot switching)		1	_	switching cycles	

Maximum power for any connected through path as stated; maximum power into any internal termination is 1W
 Hot switching powers above this level will degrade the switch lifetime

#### ABSOLUTE MAXIMUM RATINGS<sup>3</sup>

Parameter	Ratings
Operating Temperature	0°C to +40°C
Storage Temperature	-15°C to +85°C
DC Voltage max.	+26 V

<sup>3.</sup> Permanent damage may occur if any of these limits are exceeded.

#### **CONNECTIONS**

24V <sub>DC</sub> IN	(2.1 mm center positive DC Socket)
RF Switch A (1, COM, 2)	(SMA female)
RF Switch B (1, COM, 2)	(SMA female)
RF Switch C (1, COM, 2)	(SMA female)
RF Switch D (1, COM, 2)	(SMA female)
RF Switch E (1, COM, 2)	(SMA female)
RF Switch F (1, COM, 2)	(SMA female)
RF Switch G (1, COM, 2)	(SMA female)
RF Switch H (1, COM, 2)	(SMA female)
USB	(USB type B receptacle)
Network (Ethernet/LAN)	(RJ45 socket)




### RF Switch Matrix

RC-8SPDT-A18


50Ω DC to 18 GHz SMA-Female

#### **SWITCHING CONFIGURATION (PER SWITCH):**

- Fail-Safe
- Absorptive (Internal terminations on ports J1-J2)



#### **OUTLINE DRAWING (LM1852)**



Weight: 2240 grams.

S/N LABEL

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03 inch; 3 Pl. ±.015 inch.



## RF Switch Matrix


RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female


#### **TYPICAL SWITCHING PERFORMANCE**

The graphs below present the typical mechanical switching characteristic from the point of applying the internal DC voltage to the switch actuator (identified by the purple "trigger" trace). USB / Ethernet communication delays are excluded (in the order of several ms , depending on PC / network performance). The break before make process is visible in the sequence of events (the active switch path is disconnected, prior to connecting the final switch path).

#### Switching from COM<>1 to COM<>2 state: 6.95 ms



#### Switching from COM<>2 to COM<>1 state: 4.88 ms



# RF Switch Matrix

RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female

2000

4000

0.30


0.25

0.20 usertion Loss (dB) 0.15 0.15

0.05

0.00


#### **TYPICAL PERFORMANCE CURVES**




8000 10000 12000 14000 16000 18000

#### Isolation

Frequency (MHz)



#### **VSWR**





## RF Switch Matrix

RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female

#### **SOFTWARE SPECIFICATIONS**

#### **SOFTWARE & DOCUMENTATION DOWNLOAD:**

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from www.minicircuits.com/softwaredownload/rfswitchcontroller.html
- Please contact testsolutions@minicircuits.com for support

#### **MINIMUM SYSTEM REQUIREMENTS:**

Parameter	Requirements		
Interface	USB HID & Ethernet (HTTP & Telnet)		
	GUI Windows 98 or later		
System Requirements	USB API DLL	Windows 98 or later and programming environment with ActiveX or .NET support	
	USB Direct Programming	Linux, Windows 98 or later	
	Ethernet	Windows, Linux or Mac computer with a network port and Ethernet TCP/IP support	
Hardware	Pentium II or later with 256 MB RAM		

#### **APPLICATION PROGRAMMING INTERFACE (API)**

#### **ETHERNET SUPPORT:**

- Simple ASCII / SCPI command set for attenuator control
- Communication via HTTP or Telnet
- Supported by most common programming environments

#### **USB SUPPORT (WINDOWS):**

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments (refer to application note AN-49-001 for summary of supported environments)

#### **USB SUPPORT (LINUX):**

Direct USB programming using a series of USB interrupt codes

Full programming instructions and examples available for a wide range of programming environments / languages.




### RF Switch Matrix

RC-8SPDT-A18


50Ω DC to 18 GHz SMA-Female

#### **GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES**

- Connect via USB or Ethernet
- Run GUI in "demo mode" to evaluate software without a hardware connection



- View and set switch states at the click of a button
- · Configure and run timed switching sequences
- Set start-up switch state
- Configure Ethernet IP Settings





# RF Switch Matrix

RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female

#### **ORDERING INFORMATION**

Please contact Mini-Circuits' Test Solutions department for price and availability: testsolutions@minicircuits.com

Model	Description
RC-8SPDT-A18	USB & Ethernet controlled SPDT switch matrix

Included Accessories	Part No.	Description
	AC/DC-24-3W1	AC/DC 24V <sub>DC</sub> Grounded Power Adaptor. Operating temperature: 0°C to +40°C, I <sub>Max</sub> =2.5A
See Below	CBL-3W1-XX	AC Power Cord (Select one power cord from below with each Switch Matrix box)
	USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)

AC Power Cords <sup>5</sup>	Part No.	Description
	CBL-3W1-US	Power Cord for United States
-	CBL-3W1-EU Power Cord for Europe	
4	CBL-3W1-UK	Power Cord for United Kingdom
9	CBL-3W1-AU	Power Cord for Australia and China
•	CBL-3W1-IL	Power Cord for Israel

<sup>5.</sup> If you need a Power cord for a country not listed please contact testsolutions@minicircuits.com

#### **OPTIONAL ACCESSORIES**

USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)
USB-CBL-AB-7+	6.8 ft (2.1 m) USB Cable: USB type A(Male) to USB type B(Male)
USB-CBL-AB-11+	11 ft (3.4 m) USB Cable: USB type A(Male) to USB type B(Male)
CBL-RJ45-MM-5+	5 ft (1.5 m) Ethernet cable: RJ45(Male) to RJ45(Male) Cat 5E cable
BKT-272-08+	Bracket (One set of 2 each)

#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

