

# Engineering Development Model

## Voltage Controlled Oscillator

ROS-ED14934/1

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.

At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK1113

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	3479		3481	MHz
Tuning Voltage	.5		4.5	V
Power Output		6		dBm
Phase Noise				
at 1 kHz offset		-93		dBc/Hz
at 10 KHz offset		-118		dBc/Hz
at 100 KHz offset		-128		dBc/Hz
at 1000 kHz offset		-148		dBc/Hz
Pulling at 12 dBm PK-PK all phases		.5		MHz
Pushing at $V_{cc} \pm 5\%$		.2		MHz/V
Tuning Sensitivity		4-5		MHz/V
Harmonic Suppression		-18		dBc
3 dB Modulation Bandwidth		170,000		kHz
Supply Voltage		8		V
Supply Current			35	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage ( $V_{cc}$ )	+10V
Absolute Tuning Voltage ( $V_{tune}$ )	+6V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS



REV. X1  
ROS-ED14934/1  
9/21/2012  
Page 1 of 1