

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED6220/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CH549

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1640		1720	MHz
Tuning Voltage	0.5		4.5	V
Power Output		+4		dBm
Phase Noise				
at 1 kHz offset		-79		dBc/Hz
at 10 KHz offset		-104		dBc/Hz
at 100 KHz offset		-125		dBc/Hz
at 1000 kHz offset		-141		dBc/Hz
Pulling at 12 dBm PK-PK all phases		0		MHz
Pushing at Vcc=5V±0.25V		2		MHz/V
Tuning Sensitivity		26 - 40		MHz/V
Harmonic Suppression		-24		dBc
3 dB Modulation Bandwidth		2000		kHz
Supply Voltage		4.2		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+6.2V
Absolute Tuning Voltage (Vtune)	+6.5V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	8
GROUND	2,3,4,6,7,9,10,11,12