

# **RLM-512-4WL+**

50 to 512 MHz  $50\Omega$ Broadband

# **The Big Deal**

- Very high CW input power, 4 W
- Very low limiting output power, ≤3 dBm typ.
- Very fast response time, 2 nsec



CASE STYLE: CK1246-1

## **Product Overview**

The RLM-512-4WL+ protects against ESD and input power surges over a frequency range of 50 to 512 MHz, at power up to 4 W. Construction is on a micro strip low loss dielectric material and cased into a high volume, low cost package for cost efficiencies. Measuring 0.5 x 0.5 x 0.18" high, these tiny units provide excellent protection of low noise amplifiers in hostile environments where unwanted signals prevail, such as in manufacturing sites, train tunnels, etc.

# **Key Features**

Feature	Advantages
Limiting abilities from 5 to +36 dBm RF input	Protects against strong undesired signals and prevents burn out of amplifiers and highly sensitive components
3 dBm typ. output power	Low power output prevents saturation of amplifiers following the limiter
Frequency coverage 50 to 512 MHz	Protection against many sources generating unwanted signals
Response time 2 nsec	Reacts almost instantaneously to limit unwanted high-level signals
Recovery time 8 nsec	Minimal downtime after unwanted signals are removed, with very quick restoration of standard operating levels
Small surface-mount package	Allows convenient placement in amplifiers incorporating this protective device
Low cost	Practical, low-cost solution to protect expensive amplifiers or other sensitive applications from burning out

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits specification established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchaspers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

# Limiter

# **RLM-512-4WL+**

Generic photo used for illustration purposes only

## CASE STYLE: CK1246-1

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### 50 to 512 MHz **Broadband** $50\Omega$

**Features** 

• aqueous washable

**Applications** • military, hi-rel applications

· low cost

· low insertion loss, 0.58 dB typ.

• stabilizing generator outputs reducing amplitude variations • protects low noise amplifiers and other devices from ESD or input power damage

• very low output power 3 dBm typ. at 36 dBm input

## **Maximum Ratings**


-40°C to 85°C				
-55°C to 100°C				
5W				

#### Permanent damage may occur if any of these limits are exceeded

#### **Pin Connections**

INPUT	2
OUTPUT	10
GROUND	all others

## **Outline Drawing**




#### Outline Dimensions (inch )

ı		,								
ı	K	J	Н	G	F	E	D	С	В	Α
									.500	
	1.52	13.72	1.02	1.52	2.92	2.03	2.54	4.57	12.70	12.70
ı										
ı	wt		Т	S	R	Q	Р	N	M .135	L
	grams		.070	.150	.070	.140	.115	.135	.135	.100
ı	1.0		1.78	3.81	1.78	3.56	2.92	3.43	3.43	2.54

Electrical Specifications									
Parameter	Condition	Min.	Тур.	Max.	Units				
Frequency Range		50		512	MHz				
Linear Range									
Max Input Power	less than 0.1 dB compression	_	_	-10	dBm				
Insertion Loss	less than -10 dBm input power	_	0.6	1.5	dB				
VSWR	less than -10 dBm input power	_	1.4	1.85	:1				
imiting Range									
Input Power	>1dB compression filtered signal frequency	+5	_	+36	dBn				
Output Power		_	3	_	dBn				
	Input Power Range (dBm)								
4 Outmort / 4 dal D. Immort	5 to 15	_	0.21	_	4D/4				
∆ Output/ ∆ 1dB Input	15 to 20	_	0.23	_	dB/dB				
	20 to 25	_	0.15	_					
	25 to 36								
Recovery Time	y Time 1 watt pulse 50 µsec PW 1kHz duty cycle recovery by to within 90% of final value. 8				nse				
Response Time	-30 to +30 dBm input 50 μsec PW 1 kHz duty cycle	_	2	_	nse				

#### Demo Board MCL P/N: TB-613+ Suggested PCB Layout (PL-343



1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030"  $\pm$  .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


## **Typical Performance Data**


Freq. (MHz)	I. Loss (dB) in Linear	VSWR (:1) in Linear		Output 3m)		∆ Output / ∆ 1dB Input					
	Range at -10 dBm	Range at -10 dBm	+5 dBm Input	+15 dBm Input	+20 dBm Input	+25 dBm Input	+36 dBm Input	+5 to +15 dBm Input	+15 to +20 dBm Input	+20 to +25 dBm Input	+25 to +36 dBm Input
50.00 60.00 70.00 80.00 90.00 100.00 120.00 140.00 200.00 300.00 400.00 500.00	0.40 0.35 0.32 0.30 0.29 0.29 0.29 0.30 0.36 0.44 0.53 0.63	1.15 1.15 1.16 1.16 1.16 1.16 1.17 1.20 1.26 1.32 1.39 1.40	-3.10 -2.98 -2.76 -2.51 -2.25 -2.02 -1.59 -1.28 -0.73 -0.65 -0.82 -1.01 -0.99	-3.16 -3.06 -2.72 -2.27 -1.80 -1.24 -0.42 0.27 1.45 1.57 0.81 0.07	-2.62 -2.35 -1.83 -1.15 -0.52 0.07 1.00 1.67 2.73 2.09 0.95 0.17	-1.73 -1.31 -0.76 -0.13 0.36 0.60 1.66 2.26 2.97 2.04 0.81 -0.02 -0.07	-2.55 -1.53 -0.42 0.49 1.17 1.63 2.29 2.77 3.57 2.67 1.54 0.69 0.23	-0.006 -0.008 0.004 0.024 0.045 0.078 0.117 0.155 0.218 0.222 0.163 0.108	0.11 0.14 0.18 0.22 0.26 0.26 0.28 0.28 0.28 0.10 0.03 0.02	0.18 0.21 0.21 0.20 0.18 0.11 0.12 0.05 -0.01 -0.03 -0.04	-0.07 -0.02 0.03 0.06 0.07 0.09 0.05 0.05 0.06 0.07 0.06

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp













Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp