

# Voltage Controlled Oscillator ROS-2800-719R+

50Ω 1400 to 2800 MHz

## The Big Deal:

- Wide Band
- Low Phase Noise
- Robust design and construction
- Small size .500" x .500" x .180"



CASE STYLE: CK605

## Product Overview:

The ROS-2800-719R+ is a Voltage Controlled Oscillator, designed to operate from 1400 to 2800 MHz for instrumentation applications. The ROS-2800-719R+ is packaged in a metal case (size of .500" x .500" x .180") to shield against unwanted signals and noise.

## Key Features

Feature	Advantages
Wide Band: from 1400 to 2800 MHz	The model's wide bandwidth makes it suitable for a wide variety of applications, such as: CATV, military, test equipment etc...
Low Phase Noise: -91 dBc/Hz typ at 10kHz offset	Low phase noise improves system EVM (Error Vector Magnitude).
Good Pulling, 6 MHz typ.	Improves immunity against changes in output load.
Good Pushing, 4 MHz/V typ.	Provides increased immunity against noisy DC lines and improves output frequency stability vs. variations in supply voltage.
Robust design and construction	Each internal component of the ROS-2800-719R+ is bonded to the substrate, providing better immunity to microphonics, reduced phase hit, and decreased tombstoning risk during subsequent reflow operations.
Small size, .500" x .500" x .180"	The small size enables the ROS-2800-719R+ to be used in compact designs.

Wide Band 1400 to 2800 MHz

### Features

- low phase noise, -91 dBc/Hz typ. @ 10kHz offset
- low pulling, 6 MHz typ.
- low pushing, 4 MHz/V typ.
- aqueous washable



CASE STYLE: CK605

### Applications

- instrumentation
- cable TV
- lab

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)		HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER	
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)	SENSITIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.	Typ.	Typ.	Typ.			Typ.	Max.
ROS-2800-719R+	1400	2800	+3.5	-63	-91	-113	-134	0.5	25	42-107	80	10	-90	-15	-	6	4	5	30	

### Pin Connections

RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

### Maximum Ratings

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	27V
All specifications	50 ohm system


Permanent damage may occur if any of these limits are exceeded.

### Tape & Reel: F37


7" Reels with 10, 20, 50, 100 devices  
13" Reels with 200, 500 devices

### Environmental Ratings: ENV65

### Outline Drawing




### PCB Land Pattern



METALLIZATION  
 SOLDER RESIST

### Demo Board MCL P/N: TB-10 Suggested PCB Layout (PL-012)



#### NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Outline Dimensions (inch/mm)







A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
.500	.180	.100	.080	.115	.060	.040	.540	.060	1.00	.135	.135	.115	.140	.070	.150	.070		grams
12.70	4.57	2.54	2.03	2.92	1.52	1.02	13.72	1.52	2.54	3.43	3.43	2.92	3.56	1.78	3.81	1.78		1.0

# Performance Data & Curves\*

# ROS-2800-719R+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 2100 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	68.86	1291.5	1259.7	1228.4	5.54	5.05	4.08	24.06	-14.9	-18.3	-42.2	1.18	2.66	-61.31	-85.7	-108.0	-128.9	1.0	-67.54
0.50	66.80	1323.5	1294.1	1265.7	5.48	4.95	3.95	24.02	-14.8	-18.4	-40.3	0.71	3.30	-61.11	-86.5	-108.7	-129.5	2.0	-75.03
2.00	68.27	1418.8	1393.3	1372.7	5.15	4.79	3.57	23.94	-14.7	-18.8	-36.5	0.72	2.89	-61.98	-87.9	-110.3	-130.9	3.5	-81.67
3.00	74.55	1486.0	1461.6	1447.3	5.08	4.50	2.99	23.92	-14.4	-18.2	-36.4	1.55	2.84	-63.78	-88.8	-111.4	-132.1	6.0	-87.08
4.00	82.42	1558.6	1536.1	1528.1	4.79	4.21	2.52	23.88	-14.3	-18.4	-37.1	2.97	1.75	-64.16	-90.2	-112.6	-133.2	8.5	-92.27
6.00	95.53	1718.5	1709.4	1706.2	4.08	3.35	1.73	23.69	-19.0	-22.7	-34.1	5.09	3.42	-66.92	-92.4	-114.5	-135.1	10.0	-93.30
8.00	96.07	1913.1	1901.9	1896.6	3.47	2.89	1.39	23.57	-21.0	-33.9	-30.7	4.42	1.63	-66.49	-92.8	-115.3	-135.8	20.8	-101.47
9.00	92.95	2010.0	1998.0	1991.3	3.31	2.75	1.40	23.59	-21.4	-35.9	-30.8	3.55	2.12	-66.92	-93.7	-116.2	-136.9	35.5	-106.49
10.00	89.72	2104.0	2091.0	2082.6	3.19	2.78	1.55	23.61	-21.4	-32.2	-31.0	3.24	2.00	-64.65	-93.8	-116.2	-136.9	60.7	-112.01
11.00	85.50	2194.0	2180.7	2170.9	3.29	2.81	1.58	23.64	-21.9	-29.0	-31.9	3.04	1.05	-65.74	-93.0	-116.5	-137.2	86.7	-114.97
12.00	81.35	2279.9	2266.2	2255.8	3.35	2.83	1.64	23.67	-22.8	-28.4	-34.7	2.87	0.53	-66.27	-92.8	-116.7	-137.4	100.0	-116.24
13.00	77.87	2361.8	2347.5	2336.5	3.32	2.69	1.59	23.70	-23.3	-26.7	-37.5	2.59	0.43	-65.42	-93.2	-116.6	-137.5	148.1	-119.96
14.00	73.60	2440.3	2425.4	2413.5	3.21	2.73	1.64	23.73	-23.4	-24.7	-40.8	2.43	1.17	-63.53	-92.8	-116.5	-137.5	177.0	-121.66
16.00	65.13	2583.8	2568.2	2555.3	3.23	2.64	1.52	23.75	-25.8	-22.8	-33.5	2.33	0.76	-63.67	-91.7	-115.7	-136.8	211.6	-123.27
18.00	55.58	2709.2	2693.3	2679.2	3.19	2.60	1.58	23.77	-27.1	-22.7	-32.2	2.56	1.55	-64.21	-92.1	-116.2	-137.3	302.4	-126.51
19.00	51.43	2765.0	2748.8	2735.1	3.05	2.60	1.70	23.79	-28.1	-21.5	-31.6	2.74	1.84	-64.18	-92.7	-116.3	-137.5	361.5	-128.01
20.00	46.88	2816.5	2800.3	2784.4	3.11	2.54	1.45	23.78	-28.0	-21.0	-30.8	3.56	1.09	-63.84	-90.4	-115.2	-136.5	507.5	-131.07
21.00	43.67	2864.0	2847.1	2831.1	3.07	2.58	1.55	23.76	-29.0	-19.9	-31.0	3.73	1.48	-63.47	-91.0	-115.4	-136.9	606.7	-132.71
23.00	36.73	2948.2	2931.3	2913.7	3.08	2.51	1.43	23.75	-28.7	-20.1	-31.0	4.59	0.70	-63.18	-90.3	-114.9	-136.4	851.6	-135.72
25.00	31.06	3020.1	3003.2	2983.7	3.00	2.39	1.35	23.75	-27.5	-21.2	-31.9	5.13	0.81	-60.30	-89.3	-114.4	-135.8	1000.0	-137.02

\*at 25°C unless mentioned otherwise



## Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

