


## Engineering Development Model

### Voltage Controlled Oscillator

ROS-ED11616/1

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : CK605

Please click "Back", and then click "Contact Us" for Applications support.

| ELECTRICAL SPECIFICATIONS 50Ω      |      |         |      |        |
|------------------------------------|------|---------|------|--------|
| Parameter                          | Min. | Typ.    | Max. | Units  |
| Frequency                          | 1955 |         | 2030 | MHz    |
| Tuning Voltage                     | 1    |         | 9    | V      |
| Power Output                       |      | +5      |      | dBm    |
| Phase Noise                        |      |         |      |        |
| at 1 kHz offset                    |      | -86     |      | dBc/Hz |
| at 10 KHz offset                   |      | -109    |      | dBc/Hz |
| at 100 KHz offset                  |      | -129    |      | dBc/Hz |
| at 1000 kHz offset                 |      | -149    |      | dBc/Hz |
| Pulling at 12 dBr PK-PK all phases |      | 1       |      | MHz    |
| Pushing at Vcc=5V±0.25V            |      | 0.2     |      | MHz/V  |
| Tuning Sensitivity                 |      | 15 - 18 |      | MHz/V  |
| Harmonic Suppression               |      | -18     |      | dBc    |
| 3 dB Modulation Bandwidth          |      | 177000  |      | kHz    |
| Supply Voltage                     |      | 10      |      | V      |
| Supply Current                     |      |         | 30   | mA     |

| MAXIMUM RATINGS                 |                |
|---------------------------------|----------------|
| Operating Temperature           | -55°C to 85°C  |
| Storage Temperature             | -55°C to 100°C |
| Absolute Supply Voltage (Vcc)   | +12V           |
| Absolute Tuning Voltage (Vtune) | +11V           |

| PIN CONNECTIONS |                                |
|-----------------|--------------------------------|
| RF OUT          | 10                             |
| VCC             | 14                             |
| V-TUNE          | 2                              |
| GROUND          | 1,3,4,5,6,7,8,9,11,12,13,15,16 |