

Engineering Development Model

Voltage Controlled Oscillator

ROS-EDR11297

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-2041

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	2400		4500	MHz
Tuning Voltage	0.25		18.0	V
Power Output		+6.5		dBm
Phase Noise				
at 1 kHz offset		-52		dBc/Hz
at 10 KHz offset		-84		dBc/Hz
at 100 KHz offset		-109		dBc/Hz
at 1000 kHz offset		-129		dBc/Hz
Pulling at 12 dBr PK-PK all phases		11.3		MHz
Pushing at Vcc=10V±0.5V		1.5		MHz/V
Tuning Sensitivity		101 - 178		MHz/V
Harmonic Suppression		-35		dBc
3 dB Modulation Bandwidth		40000		kHz
Supply Voltage		10		V
Supply Current			33	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+10.5V
Absolute Tuning Voltage (Vtune)	+20V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

