

## Engineering Development Model

### Voltage Controlled Oscillator

ROS-EDR4266

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.

At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : CK605

#### ELECTRICAL SPECIFICATIONS 50Ω

Parameter	Min.	Typ.	Max.	Units
Frequency	1124		1718	MHz
Tuning Voltage	2		20	V
Power Output		+14		dBm
Phase Noise				
at 1 kHz offset		-71		dBc/Hz
at 10 KHz offset		-98		dBc/Hz
at 100 KHz offset		-115		dBc/Hz
at 1000 kHz offset		-139		dBc/Hz
Pulling at 12 dBm PK-PK all phases		26		MHz
Pushing at Vcc=5V±0.25V		2		MHz/V
Tuning Sensitivity		18 - 50		MHz/V
Harmonic Suppression		-13	-10	dBc
3 dB Modulation Bandwidth		2500		kHz
Supply Voltage		8		V
Supply Current			27	mA

#### MAXIMUM RATINGS

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+10V
Absolute Tuning Voltage (Vtune)	+22V

#### PIN CONNECTIONS

RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16