

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED12489A/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DV874

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	136		174	MHz
Tuning Voltage	.5		10	V
Power Output		0		dBm
Phase Noise	at 1 kHz offset	-94		dBc/Hz
	at 10 KHz offset	-117		dBc/Hz
	at 100 KHz offset	-137		dBc/Hz
	at 1000 kHz offset	-157		dBc/Hz
Pulling at 12 dBm PK-PK all phases		.02		MHz
Pushing at Vcc ± 5%		.1		MHz/V
Tuning Sensitivity		4-5		MHz/V
Harmonic Suppression		-25		dBc
3 dB Modulation Bandwidth		10,000		kHz
Supply Voltage		5		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7V
Absolute Tuning Voltage (Vtune)	+12V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
MODULATION	6
GROUND	1,3,4,5,7,8,9,11,12,13,15,16



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS



REV. X2

ROS-ED12489A/2

12/17/2008

Page 1 of 1