

# Engineering Development Model


## Voltage Controlled Oscillator

## ROS-ED12663/3

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : CK1113

### ELECTRICAL SPECIFICATIONS 50Ω

Parameter	Min.	Typ.	Max.	Units
Frequency	998		1002	MHz
Tuning Voltage	0.5		6	V
Power Output		0		dBm
Phase Noise				
at 1 kHz offset		-95		dBc/Hz
at 10 KHz offset		-125		dBc/Hz
at 100 KHz offset		-145		dBc/Hz
at 1000 kHz offset		-160		dBc/Hz
Pulling at 12 dBm PK-PK all phases		0.1		MHz
Pushing at Vcc=6V±0.25V		0.15		MHz/V
Tuning Sensitivity		5-6		MHz/V
Harmonic Suppression		-20		dBc
3 dB Modulation Bandwidth		220000		kHz
Supply Voltage		6		V
Supply Current			40	mA

### MAXIMUM RATINGS

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+8V
Absolute Tuning Voltage (Vtune)	+8V

### PIN CONNECTIONS

RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16