

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED13351/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DV897

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	763		870	MHz
Tuning Voltage	.4		4.6	V
Power Output		0		dBm
Phase Noise				
at 1 kHz offset		-85		dBc/Hz
at 10 KHz offset		-110		dBc/Hz
at 100 KHz offset		-130		dBc/Hz
at 1000 kHz offset		-150		dBc/Hz
Pulling at 12 dBm PK-PK all phases		.8		MHz
Pushing at Vcc ± 5%		1.5		MHz/V
Tuning Sensitivity		25-42		MHz/V
Harmonic Suppression		-20		dBc
3 dB Modulation Bandwidth		100,000		kHz
Supply Voltage		5		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+6V
Absolute Tuning Voltage (Vtune)	+6V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
MODULATION	6
GROUND	1,3,4,5,7,8,9,11,12,13,15,16



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



RF/MICROWAVE COMPONENTS



REV. X1
ROS-ED13351/2
12/18/2008
Page 1 of 1