

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED13409/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK1113

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	2575		3030	MHz
Tuning Voltage	.5		18	V
Power Output		7		dBm
Phase Noise	at 1 kHz offset	-78		dBc/Hz
	at 10 KHz offset	-105		dBc/Hz
	at 100 KHz offset	-125		dBc/Hz
	at 1000 kHz offset	-145		dBc/Hz
Pulling at 12 dBm PK-PK all phases		6		MHz
Pushing at Vcc ± 5%		1		MHz/V
Tuning Sensitivity		37-46		MHz/V
Harmonic Suppression		-20		dBc
3 dB Modulation Bandwidth		260,000		kHz
Supply Voltage		8		V
Supply Current			40	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+10V
Absolute Tuning Voltage (Vtune)	+20V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

