

# Engineering Development Model

## Voltage Controlled Oscillator

ROS-ED14626/1

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK1113

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1039		1072	MHz
Tuning Voltage	0		5	V
Power Output		0		dBm
Phase Noise	at 1 kHz offset	-87		dBc/Hz
	at 10 KHz offset	-115		dBc/Hz
	at 100 KHz offset	-135		dBc/Hz
	at 1000 kHz offset	-154		dBc/Hz
Pulling at 12 dB <sub>r</sub> PK-PK all phases		.3		MHz
Pushing at V <sub>cc</sub> ± 5%		.2		MHz/V
Tuning Sensitivity		15-18		MHz/V
Harmonic Suppression		-25		dBc
3 dB Modulation Bandwidth		28,000		kHz
Supply Voltage		5		V
Supply Current			30	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (V <sub>cc</sub> )	+6V
Absolute Tuning Voltage (V <sub>tune</sub> )	+6V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

